




REV.	DATE	ECR NO.	DESCRIPTION
NC	04/06/06	—	INITIAL RELEASE
A	11/14/06	—	REVISE CONTACT DIMENSION TO .0 ~ .30
B	01/17/07	—	REVISE CONTACT DIMENSION TO .00
C	09/15/08	—	REVISE OUTER BODY SHAPE

1/4-36UNS-2A



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex SMA P.C.B. – SURFACE MOUNT CENTER CONTACT (EXTENDED LEGS)								
8					DRAWN	GRS	09/15/08										
7					CHECKED												
6					ISSUED												
5	RING	BRASS	GOLD		1	SHEET	1 OF 1			PART DESCRIPTION							
4	INSULATOR	PTFE	NATURAL		1								SMA P.C.B. – SURFACE MOUNT CENTER CONTACT (EXTENDED LEGS)				
3	CONTACT PIN	BER. COPPER	GOLD		1								PART NO.				
2	INSULATOR	PTFE	NATURAL		1								132134–15				
1	BODY	BRASS	GOLD		1								DWG. NO.				
DESCRIPTION					MATERIAL	FINISH	QTY	C:/132/132134–15.DWG				132134–15.DWG			REV. C	SIZE A	SCALE NA