

HeadsUp Lite 2620

www.pelicanproducts.us



HeadsUp Lite™ 2620 Flashlight

A hybrid LED/Xenon hands-free flashlight. The 2620 gives you the option of using the Xenon lamp for intense bright light or 3 LEDs to conserve battery life. The multi-angle pivoting head allows you to aim light where you need it. A rubber strap for hard hat use and adjustable cloth strap for bare head use are both included. The HeadsUp Lite 2620 is perfect for hiking, camping, or for any task that require both hands. Powered by 3 AAA alkaline cells (included)

Minimum Pack 1 ea.

Packaged Weight: 8.3 oz.

HeadsUp Lite™ 2620 Flashlight Specifications

	High	Low
LIGHT SOURCE	Xenon (High)	LED (Low)
BATTERIES	3 AAA Alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	4.5	
LENGTH	2.16" (5.5 cm)	
WEIGHT w/ BATTERIES	4.8 oz. (0.14 kg)	
WEIGHT w/o BATTERIES	3.5 oz. (0.1 kg)	

	FL 1 STANDARD	High	Low
LIGHT OUTPUT		26 LUMENS	14 LUMENS
RUNTIME (hours/min)		2h 15m	18h
BEAM DISTANCE (meters)		44m	29m
PEAK BEAM INTENSITY (candela)		491cd	216cd

HeadsUp Lite™ 2620 Flashlight Configurations

Cat. #	Description
2620	HeadsUp Lite™ 2620 Flashlight (Carded)

NSN List

NSN #	Description
6230-01-513-8446	2620RS Black

HeadsUp Lite™ 2620 Flashlight Accessories

Cat. #	Description
2624	HeadsUp Lite™ 2620 Lamp
2625	Red LED Flashing/Constant Alert Light
2626	Replacement Rubber Strap
2627	Replacement Cloth Strap

HeadsUp Lite™ 2620 Flashlight Approvals



II 3 G EEx nL IIC T3X

Certificate: TRL Report# XU1006/4804



Class I, Div. 1, GP C,D, T3C CONFORMS TO STD. UL 783