




Rectifiers, General Purpose

(Continued)

I_O (AMPS)	2.0		3.0		
@ T_A (°C)	75	50	75	55	75
I_{FSM} (AMPS)	50	50	200	100	125
CASE					
	GPR-1A	DO-15	DO-201AD	GPR-3A	
V_{RRM} (VOLTS)					
50			1N5400		
100	CPR2-010	CR2-010	1N5401		
200	CPR2-020	CR2-020	1N5402	1N5550	1N5624
300			1N5403		
400	CPR2-040	CR2-040	1N5404	1N5551	1N5625
500			1N5405		
600	CPR2-060	CR2-060	1N5406	1N5552	1N5626
800	CPR2-080	CR2-080	1N5407	1N5553	1N5627
1000	CPR2-100	CR2-100	1N5408	1N5554	
1200	CPR2-120	CR2-120			
1400		CR2-140			
1600		CR2-160			

V_F MAX @ $I_F = I_O$	1.2V	1.1V	1.1V	1.1V	1.0V
-------------------------	------	------	------	------	------

I_R MAX @ V_{RRM}	5.0μA	10μA	10μA	1.0μA	5.0μA
-----------------------	-------	------	------	-------	-------