


Low force position detectors



- Conforms to standard DIN 43365 Form A
- Low activation force < 1.7 oz. (50 g @ 6 bars) at 90 psi
- No continuous consumption of compressed air



Part numbers

Function	NO	81 290 501	—
	NC	—	81 290 001

Symbol




Characteristics


Orifice diameter	inches(mm)	5/64" (2)	5/64" (2)
Operating pressure	psi(bar)	30 > 120 (2 > 8)	30 > 120 (2 > 8)
Flow at 60 psi(4 bars)	cfm(Nl/min)	4.5 (130)	2.5 (>70)
Activation force at 90 (6 bars)	ounces(g)	<1.7 (< 50)	<1.7 (< 50)
Permissible fluid: air, inert gases			
Max/min. of fluid temperatures	°F(°C)	+20> +120 (-10 > +50)	+20> +120 (-10 > +50)
operating	°F(°C)	+20> +140 (-10 > +60)	+20> +140 (-10 > +60)
storage	°F(°C)	+20> +160 (-40 > +70)	+20> +160 (-40 > +70)
Mechanical life at 90psi (6 bars)	cycles	10 million	10 million
Response on activation	ms	≤ 15	≤ 15
time on release	ms	≤ 15	≤ 15
Barb connection for semi-rigid tubing	inches(mm)	0.106" I.D.x 5/32" O.D. (2.7x4)	0.106" I.D.x 5/32" O.D. (2.7x4)
Weight	grams	8.5	8.5

Principle of NC operation

Deactivated




Activated




Operation accessories

Unless otherwise requested, flat and roller-ended levers are supplied loose.


161 A
flat
79 215 741




161 G
roller
70 507 529



Dimensions




161 A



161 E

79 215 742



Use (metric) dimensions for critical data

Other information	To order, specify :
On request : Wide range of actuators Connectable exhaust	Standard products 1 Part number 2 Accessory Example : Low force position detector 81 290 501 Flat lever 79 215 741

Products and specifications subject to change without notice.

Order/Technical Support – Tel: (800) 677-5311 / FAX: (800) 677-3865 / www.crouzet-usa.com

