




MARKETING SALES DRAWING

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



MOUNTING HARDWARE



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4400-033.
TUSONIX RoHS COMPLIANT PART NUMBER: 4400-033 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD, BUSHING, AND MOUNTING HARDWARE: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS. STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. OPERATING TEMPERATURE RANGE : -55°C TO +125°C.
5. MAX. RECOMMENDED SOLDERING TEMPERATURE: 260°C.
6. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
7. MAX. RECOMMENDED MOUNTING TORQUE - 2.0 lb.-in. [.226 Nm].

CAP.(pf)	TOLERANCE	DC WORKING VOLTAGE		I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220				
		85°C	125°C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
2700	GMV	150	100	10 G Ω	250	10	----	10	25	40	50

REVISION RECORD Original Release C.O. 20011102-1-02 VARS 035,036,037 & 1MHz COLUMN ADDED. L.E. 11-07-90 5591 RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01 20011102-1-02 REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 11-19-02 20021113-1-04 REVISED AND ADDED NOTES. S.M. 12-14-05 20051122-2-17	0 20011102-1-02		1 20011102-1-02		2 20011102-1-02		3 20021113-1-04		4 20051122-2-17	
	0 20011102-1-02		1 20011102-1-02		2 20011102-1-02		3 20021113-1-04		4 20051122-2-17	
	0 20011102-1-02		1 20011102-1-02		2 20011102-1-02		3 20021113-1-04		4 20051122-2-17	
	0 20011102-1-02		1 20011102-1-02		2 20011102-1-02		3 20021113-1-04		4 20051122-2-17	

--TOLERANCES-- Unless Otherwise Specified		DECIMAL ± NOTED		ANGLES ±		TUSONIX TUCSON, ARIZONA		Title BUSHING STYLE EMI FILTER	
DECIMAL ± NOTED		ANGLES ±		Drawn S.M. 11-08-01		Scale 5 X		Approved B.Mc. 11-08-01	
DECIMAL ± NOTED		ANGLES ±		A		4400-033			