

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFDOMETOP Bar..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click  to remove) Search Tips

Text Search: 'BT2S-M69'

BT2S-M69



- Flammability rating of UL94V-0 – indoor use
- Dome-top head features unique patented design with round, smooth edges
- Stainless steel locking barb provides consistent performance, reliability, and infinite adjustability through entire bundle range
- High strength and low thread force
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light -Heavy cross section ties have a straight tip)
- Complementary flame retardant mounts available

Part Number	BT2S-M69
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, Metal Barb, 8.0"L (203mm), Standard, Flame Retardant Nylon, Natural
Product Type	Cable Ties
Material	Flame Retardant Nylon 6.6
Color	Ivory
CSA Certified	Yes
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Length (In.)	8.0
Length (mm)	203
Width (In.)	0.185
Width (mm)	4.7
CE Compliant	Yes
Cross Section	Standard
Head Height (In.)	0.220
Head Height (mm)	5.6
Head Width (In.)	0.320
Head Width (mm)	8.1
Locking Style	Locking
Material Flammability Rating	V-0
Max. Bundle Diameter (In.)	2.00
Max. Bundle Diameter (mm)	51
Max. Continuous Use Temperature	212°F (100°C)
Min. Bundle Diameter (In.)	0.06
Min. Bundle Diameter (mm)	1.5
Min. Loop Tensile Strength (Lbs.)	50
Min. Loop Tensile Strength (N)	222
Plenum Rated	No
Pricing Description	Cable Tie, Metal Barb, 8.0"L (203mm), Standard, Flame Retardant Nylon, Natural
Thickness (In.)	0.045
Thickness (mm)	1.2
Tool	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

[Home](#) | [Industries](#) | [Solutions](#) | [Services](#) | [Products](#) | [Partners](#) | [Support](#) | [Contact Us](#) | [Site Map](#) | [Careers](#)
Copyright © 1995-2011, PANDUIT CORPORATION. All rights reserved. | [Legal Information](#) | [Privacy Policy](#)