

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0444412003](#)
Status: **Active**
Description: 7.50mm (.295") Pitch Sabre™ Receptacle Housing, Single Row, PA Polyamide Nylon 6/6, UL 94V-0, 3 Circuits, Glow Wire Compatible

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PSX-44441-9999 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	44441
Comments	Meets UL 1950 finger proof standard when mated to 43680-2003 plug loaded with 43178-5002 or 43178-6002 male terminals or when mated to a 46007 series 2 circuit, UL 94V-0 right angle header.
Product Literature Order No	USA-113
Product Name	Sabre™
Physical	
Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.295 In
Pitch - Mating Interface (mm)	7.50 mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +75°C
Electrical	
CSA	LR19980
Current - Maximum	18A
UL	E29179

Material Info

Reference - Drawing Numbers
Product Specification PSX-44441-9999
Sales Drawing SD-44441-*003



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[44441Series](#)

Mates With
436802003 Plug Housing. [43160](#) 3 Circuit, UL 94V0 Vertical or Right Angle Headers. [46007](#) 3 Circuit, UL 94V0 Right Angle, UL 1950 Finger Proof Safe Headers

Use With
[43375](#) Female Crimp Terminals