




Quartz Crystal

SMD-version


model	KX - 7
frequency	25,0 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance -20° ~ + 70°C	± 50 ppm
load capacitance C_L	12 pF
series resonance R_1 max.	50 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_O max.	5,0 pF
drive level in mW max.	0,05
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.88667



soldering condition



suggested soldering pad



(mm) reel diameter 178 mm