

Rail Mounted Terminal Blocks

910499

When good enough just isn't good enough

Weidmüller **SAK 2.5 TC**[Email to a Friend](#)

Representative Photo

Technical Information

Clamping Type	Screw Clamp
Series	SAK Series
Rail Type	TS 35
Function	Feed Through
Configuration	Thermocouple
Wire Size	#22...12 AWG
Color/Material	Beige PA
Special Requirements	Type J

Technical Data

	UL	CSA	VDE
Wire Size	#22...12 AWG	#26...12 AWG	2.5 mm ²

Additional Data

Width/Length/Height mm (in.)	12/36.5/49.5 (.47"/1.44"/1.95")
Insulation Stripping Length mm (in.)	10 (.39")
Torque Nm (lb. in)	0.8 (7.0)
Clamping Screw	M 2.5
Flammability Class	UL 94 (V2)

Suggested Accessories

DIN-rail

End bracket

End plate/partition (AP/TW)

Ferrules

Marking pens

Marking tags (DEK)

Mounting brackets

Tools

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America
United States 001 (800) 849-9343
Canada 001 (800) 268-4080

or

Weidmüller - Germany
Telephone operator 0049 (-5252) 960-0