



ETA-USA

The Power Professionals

DTA-0512FWX-W

27W



FEATURES:

- 3-pole IEC320-C6 Class I and C8 Class II AC inlet available
- 2 year warranty
- Black color plastic enclosed case



MODEL/CHANNEL		Unit	DTA27-0512FWX-W 2-Pole		DTA27-0512FWX-W 3-Pole	
OUTPUT	Output Voltage	Vdc	+5	+12	+5	+12
	Output Current Min.	A	0.5	0.1	0.5	0.1
	Output Current Max.	A	2~5	0.2~1.5	2~5	0.2~1.5
	Ripple and Noise(max.) *3	mV	50	120	50	120
	Voltage Regulations	-	±5%			
	Hold Up Time	-	10ms typical at full load @ 115VAC			
	Power	W	27W			
INPUT	Input Voltage	Vac	90VAC~264VAC			
	Input Current	A	1A@264Vac 2A@90Vac			
	Line Frequency	Hz	47Hz to 63Hz			
	Efficiency	A	>70% 115VAC at full load (DC Conversion)			
Protection	Over Voltage Protection	-	Auto Recovery			
	Short circuit protection	-	Auto Recovery			
Environmental Agencies	Safety	-	UL 1950	CSA 22.2-234	TUV EN60950	IEC 950 CE: EMC &LVD
	EMC Standards	-	FCC Class B; CISRP22 Class B; EN 55022 Class B			
	MTBF	-	>100'000 hours at full load and 25°C ambient temperature.			
Environment	Operating Temperature	-	0°C to 40°C			
	Storage Temperature	-	-10°C to +70°C			
Dimension	Size(WxHxD) / Weight	mm/g	106Lx60Wx 30H			




ETA-USA

16170 Vineyard Blvd. Suite 180 Morgan Hill, CA 95037 <http://www.eta-usa.com>
Toll-free (US only): 800-ETA-POWR (800-382-7697) Telephone: 408 778-2793 FAX: 408-779-2753



Dimension Diagram (mm)



27W





Dimension Diagram (mm)

27W



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[DTA27-0512FWX-W-3-047](#) [DTA27-0512FWX-W3](#)