



DESCRIPTION: POWER - RIGHT ANGLE - MALE



## SPECIFICATIONS:

### ELECTRICAL:

INSULATOR RESISTANCE: 5,000 MegOHMS Min.  
DIELECTRIC WITHSTANDING: 1,000VAC r.m.s.  
OPERATING TEMPERATURE: -55° C ~ +125° C  
CONTACT RESISTANCE: 30 Milliohms Max.  
POWER PINS: 40 AMPS

### MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg Max.  
CONTACT SEPARATOR FORCE: 0.3Kg Min.

### MATERIALS:

CONTACTS: BRASS  
INSULATOR: PBT UL94V-0 RATED,  
230°C PROCESS TEMP.

STEEL  
BRASS, NICKEL PLATED  
BRASS, NICKEL PLATED

SHELL: STEEL  
BOARD LOCK: BRASS, NICKEL PLATED  
CINCHNUT: BRASS, NICKEL PLATED  
BRACKET: STEEL, NICKEL PLATED

FINISH: SHELL: NICKEL

6843W3103L461

46 = 4-40 INSERTS /  
BOARD LOCKS

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE  
THE PROPERTY OF NorComp AND SHALL NOT  
BE REPRODUCED, COPIED OR USED AS THE  
BASIS FOR THE MANUFACTURE OR SALE OF  
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: C. SMITH DATE: 10-05-06



CHECKED: DATE:

SCALE: 1.5 = 1 SHEET OF 1 2 REV 2


DWG NO. 6843W3103L461

NorComp

NOTE:  
POWER CONTACTS COME  
PRE-LOADED INTO INSULATORS



40 AMP POWER CONTACT



	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN:	C. SMITH	DATE:	10-05-06
		CHECKED:		DATE:	
SCALE:	1.5 = 1	SHEET	2	OF	2
DWG NO.					REV 2
					6843W3103L461

RoHS COMPLIANT

NorComp