



Chloroprene tubing and grommets

- HS
- HT

Features and Benefits

Chloroprene tubing and grommets are highly elastic in nature. They have very good insulating characteristics and are easy to fit.

Application

For years, HellermannTyton tubing and grommets have been the engineer's preferred choice for electrical insulation and mechanical protection in a diverse range of electronic and electrical industries.

To save time and effort when fitting the tubing, try the HellermannTyton NA three pronged pliers (see Chapter 6.3) and the Hellerine lubricant (see end of Chapter), which are specially designed for use with HellermannTyton chloroprene tubing.




Chloroprene tubing.

Material Data	
Material	Chloroprene (CR)
Operating Temperature	-25 °C to +100 °C
Flammability	UL94 HB and FMVSS-302
Elongation at break	min. 400%



Other colours and cut lengths available on request. Please contact us!



Chloroprene tubing

Technical Table

Article-No.	Type	Ø D	Wall (WT) nom.	Bundle Ø max.	Reel Length (m)	Colour
Tubing						
608-00100	HS0	1.25	0.50	2.0	100	Black (BK)
608-00150	HS1	1.75	0.50	3.5	100	Black (BK)
608-00200	HS1K	2.50	0.90	4.0	100	Black (BK)
608-00250	HS2	3.00	0.60	6.0	100	Black (BK)
608-00300	HS2K	4.00	1.50	8.5	50	Black (BK)
608-00350	HS3	5.00	0.70	9.0	100	Black (BK)
608-00400	HS4	7.50	0.80	13.0	25	Black (BK)
608-00450	HS5	10.00	1.00	20.0	25	Black (BK)
608-00500	HS8	12.00	1.00	23.0	25	Black (BK)
608-00550	HS9	14.00	1.00	25.0	20	Black (BK)
608-00600	HS10	17.00	1.00	28.0	20	Black (BK)

All dimensions in mm. Subject to technical changes.

Technical Table

Article-No.	Type	Ø D	Wall (WT) nom.	Bundle Ø max.	Length (L)	Colour
Grommets						
600-10200	HT0	1.25	0.50	2.0	20	Black (BK)
600-15200	HT1	1.75	0.50	3.5	20	Black (BK)
600-20250	HT1K	2.50	0.90	4.0	25	Black (BK)
600-25250	HT2	3.00	0.60	6.0	25	Black (BK)
600-30300	HT2K	4.00	1.50	8.0	30	Black (BK)
600-35250	HT3	5.00	0.70	9.0	25	Black (BK)
600-40300	HT4	7.50	0.80	13.0	30	Black (BK)
600-45350	HT5	10.00	1.00	20.0	35	Black (BK)
600-50500	HT8	12.00	1.00	23.0	50	Black (BK)
600-55500	HT9	14.00	1.00	25.0	50	Black (BK)
600-60500	HT10	17.00	1.00	28.0	50	Black (BK)

All dimensions in mm. Subject to technical changes.



Chloroprene tubing