

6.02165.50 BSZ 14.4 Impuls

14.4 Volt Cordless Drill / Screwdriver BSZ 14.4 Impuls



- Selectible impulse mode for exact screw-driving and comfortable drilling
- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Quick-action keyless chuck and spindle stop gear for convenient one-hand tool change: Metabo "Quick"
- T-handle for optimum centre of gravity, especially for screws
- Fatigue-free operation due to perfect ergonomics
- Rubber-coated handle provides a comfortable non-slip grip for the user
- High service life due to 3-level planetary metal gears
- Gentle, spring-supported gear change
- Built-in collector fan to prevent overheating
- Bit case for two bits
- Maximum system flexibility through free combination of chargers and battery packs (within a voltage class)
- Easy and quick change of battery pack
- Li-Ion battery packs for up to 40% more power with up to 40% less weight. Long storage capacity and almost no self-discharge. No memory effect!
- With "AIR COOLED" super quick charger AC 15 Plus for charging NiCd, NiMH and Li-Ion battery packs; with refresh function; charge time approx. 15 minutes (at 1.4 Ah)

Comparative device characteristics

Type of battery pack	Li-Ion
Battery pack voltage	14,4 V
Capacity of battery pack	2,2 Ah
Maximum torque, soft	24 Nm
Pulse torque	28 Nm
Maximum torque, hard	55 Nm
Drilling capacity in	
- Steel	12 mm/5 mm
- Wood	30 mm/22 mm
No-load speeds	0 - 400 / 0 - 1.400 /min
Drilling spindle thread	1/2" - 20 UNF
Chuck capacity	1,5 - 13 mm
Weight (including battery pack)	1,8 kg

Scope of delivery

2 Li-Ion battery packs (14.4 V/2.2 Ah), "AIR COOLED" super quick charger ACS 15 Plus, carry case