









NOTES:

1. MATERIAL:

- A. HEADER HOUSING: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94 V0.
- B. TERMINAL: TINBRONZE
- C. WAFER: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT

- 2. PACKAGING ACCORDING EUR-14-005.

- 3. MARKING ACCORDING DWG 59550.

- 4. FOR MORE DETAILS REFER THE DRAWING 72844.C
(4 X6 SIGNAL SOFIX BOARD CONNECTOR)

5-ROHS: INFORMATIONS

- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECOND IN A WAVE SOLDER APPLICATION WITH A 1.6MM MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE. PACKAGING SPEC: GS-14-920.

Performance level

72800-11YLF	Telcordia CO.
72800-21YLF	Telcordia CO.

www.fciconnect.com

surface 0.8	tolerance std	projection
ISO 1302	ISO 406 ISO 1101	⊕
TOLERANCES UNLESS OTHERWISE SPECIFIED		

Dr	J.Taron	2004/11/19	ANGULAR	0.X	±0.3	size	A3	Scale	3:1
Eng	J.Taron	2004/11/19	LINEAR	0.XX	±0.15	ECN	N11-0071	Spec ref	RELEASE
Chr	P.Legare	2004/11/19	0° ±2°	0.XXX	±0.05	Product family	SOFIX	Rev.	F
Appr	P.Legare	2004/11/19	Product family	SOFIX	Spec ref	RELEASE			



title SOFIX 72 POS KIT
SHIELDED HDR 3x24 STB
catalog no

dwg no 72800

CUSTOMER sheet 1 of 2

rev	ecn no	dr	date
A	LS04-0342	JTA	2004/11/19
B	LS05-0021	JTA	2005-02-20
C	LS06-0084	LGO	2006-07-04
D	LS07-0195	JTA	2007-10-02
E	N09-0372	SH	2009-12-01
F	N11-0071	A.ZH	2011-03-23
-	-	-	-

REV F - 2006-04-17



Copyright FCI.




Copyright FCI.

REV F - 2006-04-17

Product number									
Item			Column						
	Rad Row	Number	6	5	4	3	2	1	
72800-X11LF	D	24	Q	Q	Q	Q	Q	Q	
	C		P	P	P	P	P	P	
	B		O	O	O	O	O	O	
	A		N	N	N	N	N	N	
72800-X12 LF	D	24	U	U	U	U	U	Q	
	C		T	T	T	T	P	T	
	B		S	S	S	S	S	S	
	A		N	N	N	N	N	N	
72800-X13 LF	D	12	Q	Q	Q	Q	Q	Q	
	C								
	B		O	O	O	O	O	O	
	A								

Item	DIM A
N	5.75
O	5.00
P	5.00
Q	5.00
R	5.00
S	5.75
T	5.75
U	5.75



www.fciconnect.com			surface 0.8 ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 	MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	J.Taron	2004/11/19	ANGULAR	LINEAR	0.X	±0.3	size	Scale	
Eng	J.Taron	2004/11/19			0.XX	±0.15	A3	3:1	
Chr	P.Legare	2004/11/19	0° ±2°		0.XXX	±0.05	ECN	N11-0071	
Appr	P.Legare	2004/11/19	Product family			SOFIX	Spec ref	RELEASE	
	title					dwg no	72800		Rev.
	SHIELDED HDR 3x24 STB								F
	catalog no						CUSTOMER		sheet 2 of 2