

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-R2430

CATALOG LISTING

BZ-R2430

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-17792

ISSUE

4

M

REVISIONS

A	204121
	KED
	10 OCT 01
B	204448
	CSL
	28 NOV 01
C	0033747
	MST
	12SEP07

CHECK

12SEP07

PSR

CHECK

16 DEC '89

DAW

CHECK

89

DEC


P 15

J A

FO-52848-B

RASTER

DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ——— 7-9 OZ
RELEASE FORCE ——— 4 OZ MIN
DIFFERENTIAL TRAVEL .00020-.00035
OVERTRAVEL ——— .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A 125, 250, OR 480 VAC

L34



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .060 LB

-L310-