

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74547-0301](#)
Status: **Active**
Overview: iPass™ Connector System
Description: External iPass Mini Multi-Lane SAS X4 Cable Assembly, 26 Circuits, 28 AWG, 1.0m Length, Key 2, 4, 6

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary TS-74547-001 \(PDF\)](#)

Agency Certification

CSA LR64395
UL E72548

General

Product Family Cable Assemblies
Series [74547](#)
Assembly Configuration Dual Ended Connectors
Comments Universal Key, SAS
Connector to Connector Mini SAS-to-Mini SAS
Overview [iPass™ Connector System](#)
Product Name iPass™, Mini Multi-Lane, SAS, X4
UPC 822350284455

Physical

Cable Length 1.0m
Circuits (Loaded) 26
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Stainless Steel
Net Weight 156.187/g
Packaging Type Bag
Pitch - Mating Interface 0.80mm
Single Ended No
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Parallel Pair


Electrical

Current - Maximum per Contact 1A
Shielded Yes
Voltage - Maximum 30V

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74547-100
Test Summary TS-74547-001



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74547Series](#)

Mates With
[75586](#) iPass™ Receptacle. [74548](#) EMI Housing Assembly

Use With
[74735](#) X2 Transceiver. [74739](#) XPAK Transceiver. [74548](#) External iPass Mini Multi-Lane SAS Guide Frame

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74547-0301