










- ① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.
COLOR: NATURAL.
- ② CONTACT MATERIAL: PHOSPHOR-BRONZE.
- ③ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) -
0.00127 MIN. NICKEL
ON MATING SURFACES-
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT
ON LEADS-
0.00381 MIN. TIN-LEAD, OVER UNDERPLATE


LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER TYCO SPEC 112-1002 AFTER PLATING.
- ④ PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED
APPROXIMATELY AS SHOWN.
- ⑤ CUSTOMIZED PART, HOUSING MOLDED WITHOUT END GUIDE LUGS.
- ⑥ OBSOLETE PART NUMBER.
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



TYPICAL COLD HOLD
FOR ALL ASSEMBLIES

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

56 56 56 56 7 OBSELETE SUPERCEDED BY 5536510-8 OBSELETE	YES	94	47	95.88	3	192	2-536510-4
	YES	46	23	47.88	33	96	2-536510-3
	NO	34	17	35.88	3	72	1-536510-5
	NO	22	11	23.88	33	48	1-536510-4
	NO	94	47	95.88	3	192	1-536510-3
	NO	106	53	107.88	33	216	1-536510-2
	NO	70	35	71.88	3	144	1-536510-1
	NO	130	65	131.88	33	264	1-536510-0
	NO	106	53	107.88	3	216	536510-9
	NO	118	59	119.88	33	240	536510-8
	NO	82	41	83.88	3	168	536510-7
	NO	58	29	59.88	33	120	536510-6
	NO	70	35	71.88	3	144	536510-5
	NO	94	47	95.88	33	192	536510-4
	NO	46	23	47.88	3	96	536510-3
	NO	22	11	23.88	33	48	536510-2
YES	10	5	11.88	3	24	536510-1	
POSITIONING PEGS	C	B	A	FINISH	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN C. LOCONDRÒ		09/04/92		Tyco Electronics Corporation	
		CHK S. HEADER		01/26/93		Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		TOLERANCES: UNLESS OTHERWISE SPECIFIED:		NAME		RECEPTACLE ASSEMBLY, SIGNAL MODULE, Z-PACK 2mm FB, 4 ROW, 3.5mm LEAD LENGTH	
		0 PLC ± — 2 PLC ± — 2 PLC ± .13 2 PLC ± — 4 PLC ± — ANGLES ± —		APPR D. BACFTEL 1/26/93 PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO A1 00779 C-536510	
MATERIAL 		FINISH 		WEIGHT —		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1 REV AD3	