





	22-20 AWG	.302	1-66400-0	5-862197-4
	18-16 AWG	.185	1-66099-5	5-862197-3
	18-16 AWG	.302	1-66099-5	5-862197-2
	22-20 AWG	.185	1-66400-0	5-862197-1
OBSOLETE	14 AWG	.302	66361-2	862197-8
OBSOLETE	14 AWG	.185	66361-2	862197-7
	—	.302	—	862197-6
	—	.185	—	862197-5
	22-20 AWG	.302	66400-1	862197-4
	18-16 AWG	.185	66099-2	862197-3
	18-16 AWG	.302	66099-2	862197-2
	22-20 AWG	.185	66400-1	862197-1
	WIRE GAGE REF	DIM A REF	PIN CONTACT TYPE III+ L.P. QTY = 1	PART NUMBER



1. MAX VOLTAGE:
20 KVDC
8 KVDC RMS 60 HZ
2. USE AMP CRIMP TOOL: #90067-2
3. NUT AND PIN CONTACT SUPPLIED WITH KIT UNASSEMBLED.

MOUNTING HOLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 04-MAY-01		tyco Electronics		Tyco Electronics Corporation								
		CHK D. EABY 04-MAY-01				Harrisburg, Pa 17105-3608								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. EABY 04-MAY-01		NAME								
		PRODUCT SPEC		RECEPTACLE LGH —										
		—												
		APPLICATION SPEC												
		—												
MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
—		—		—		A2	00779	C-862197	—					
CUSTOMER DRAWING						SCALE	4:1		SHEET	1	OF	1	REV	G