



## 1/4" PHONE PLUGS

Amphenol has introduced two ranges of 1/4" Phone plug connectors to satisfy the needs of the manufacturer and the end user. The PRO – a heavy duty on-road plug and the MUSICIAN - a solid performing general use plug. Both series offer different features and benefits and the most suitable type will be determined by application, budget and personal choice. The 1/4" Phone plug jacks range has been widened with the stackable (piggy back) OEM series, saving board space and manufacturing costs. The RCA and Banana plugs complete our extensive range of entertainment interconnects.

### Applications

- Audio Cables and Snakes
- Amplifiers
- Speakers
- Mixing desks
- Rack mount equipment
- Patch panels

### Features / Options – PRO RANGE 1/4" Phone Plug T-Series.

- Mono or Stereo (TRS).
- Stylised shell design with Ergonomic grip
- Silver or Gold contact plating
- Keyed Shell
- Optional heavy duty metal backshell / boot
- Great solderability
- Increased solder area on ground contact
- "Jaws" Cable Clamp
- Precision machined contacts

### Features / Options – MUSICIAN RANGE 1/4" Phone Plug

- Mono or Stereo (TRS)
- Compact Shell
- Straight or Right angle
- Stylish shell design.
- Flexible grommet cable protection
- Gold or Nickel plated tip
- Gold, Nickel or Black finish
- Machined or Diecast shell

### Features / Options – OEM RANGE 1/4" Phone Jack

- Mono or Stereo (TRS)
- Stackable (Piggy back) mounting
- Vertical or Horizontal PCB mount
- Mono and Stereo switched contacts
- Solder contacts
- Combo contacts
- Metal nut
- Plastic nut

### Features / Options – RCA Plug

- Female or Male
- Red or Black strip for channel I.D.
- Gold plated finish
- Gold plated contacts

### Features / Options – Banana Plug

- Red or Black for channel I.D.
- Gold or Nickel plated contacts

### Jaws Cable Clamp Options for T-Series



Standard Jaws cable clamp (Black), Cable O.D 3mm to 7mm (0.118" to 0.275")



Large Jaws cable clamp (Purple), Cable O.D 6mm to 8mm (0.236" to 0.314")

### Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

### Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on Page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



# Amphenol



1/4" PHONE PLUGS

T-SERIES (PRO RANGE)



### Features:

- Mono or Stereo (TRS).
- Stylised shell design with Ergonomic grip.
- Robust diecast shell in Satin nickel or Black finish.
- Silver or Gold contact plating.
- Keyed shell.
- Optional heavy duty metal backshell / boot.
- Great solderability.
- Increased solder area on ground contact.
- "Jaws" Cable Clamp.
- Precision machined contacts.
- Quick and easy assembly – by hand or portable termination tool part number T2870.

**Options:** Gold Contacts, Large or Small Jaws Cable Clamp, Black Shell, Metal Backshell / Boot, Bulk Pack.

**Part Number Breakdown:** [Page 74](#)    **Specifications:** [Page 73](#)

| PRODUCT - FIGURE | DRAWING | DESCRIPTION  | VARIATIONS           | PART NUMBER |
|------------------|---------|--|----------------------|-------------|
|                  |         | 1/4" (6.35mmø)<br>Mono Phone plug,<br>Jaws cable clamp,<br>Thermoplastic<br>backshell, Satin finish.   | Standard             | TM2P        |
|                  |         |  | Gold Plated Contacts | TM2P-AU     |
|                  |         |  | Large Cable Clamp    | TM2PJ       |
|                  |         |  | Bulk Pack            | TM2P-BULK   |
|                  |         |  | Metal Boot (Satin)   | TM2PN       |
|                  |         | 1/4" (6.35mmø)<br>Mono Phone plug,<br>Jaws cable clamp,<br>Thermoplastic<br>backshell, Black finish.   | Standard             | TM2PB       |
|                  |         |  | Gold Plated Contacts | TM2PB-AU    |
|                  |         |  | Large Cable Clamp    | TM2PBJ      |
|                  |         |  | Bulk Pack            | TM2PB-BULK  |
|                  |         |  | Metal Boot (Blk)     | TM2PBM      |
|                  |         | 1/4" (6.35mmø)<br>Stereo Phone plug,<br>Jaws cable clamp,<br>Thermoplastic<br>backshell, Satin finish. | Standard             | TS3P        |
|                  |         |  | Gold Plated Contacts | TS3P-AU     |
|                  |         |  | Large Cable Clamp    | TS3PJ       |
|                  |         |  | Bulk Pack            | TS3P-BULK   |
|                  |         |  | Metal Boot (Satin)   | TS3PN       |
|                  |         | 1/4" (6.35mmø)<br>Stereo Phone plug,<br>Jaws cable clamp,<br>Thermoplastic<br>backshell, Black finish. | Standard             | TS3PB       |
|                  |         |  | Gold Plated Contacts | TS3PB-AU    |
|                  |         |  | Large Cable Clamp    | TS3PBJ      |
|                  |         |  | Bulk Pack            | TS3PB-BULK  |
|                  |         |  | Metal Boot (Blk)     | TS3PBM      |

## 1/4" PHONE PLUG TECHNICAL DATA

|                                   |  | VALUE  |
|-----------------------------------|--|--|
| <b>GENERAL CHARACTERISTICS</b>    | Number of Contacts                           | 2 Pole (Mono)<br>3 Pole Tip Ring Sleeve (Stereo)   |
|                                   | Termination                                  | Solder   |
|                                   | Max. Wire Gauge - Stranded Wire              | 2 Pole (Mono): AWG 16~1.5mm <sup>2</sup><br>3 Pole (Stereo): AWG 18~1mm <sup>2</sup>         |
|                                   | Flammability rating of insulating plastics   | UL94V-0  |
|                                   | Solderability, complies with                 | IEC 68-2-20  |
| <b>ELECTRICAL CHARACTERISTICS</b> | Current Carrying Capacity                    | 10A (Depends on Mating Connector and Cable)  |
|                                   | Typical Contact Resistance                   | Depends on Mating Connector  |
|                                   | Insulation resistance (initial)              | >2GΩ   |
|                                   | After Damp Heat Test                         | ≥ 1GΩ  |
|                                   | Dielectric Withstand Voltage                 | 2 Pole : 1.5 kV dc<br>3 Pole : 1 kV dc   |
| <b>CLIMATIC CHARACTERISTICS</b>   | Protection Class                             | IP40   |
|                                   | Operating Temperature                        | -20C to +70C   |
| <b>MECHANICAL CHARACTERISTICS</b> | Insertion and Withdrawal Force               | ≥ 10N - ≤ 30N  |
|                                   | Weight <sup>1)</sup> Thermoplastic Backshell | 28g (0.061lb)  |
|                                   | Weight <sup>1)</sup> Metal Backshell         | 35g (0.077lb)  |
|                                   | Typical Cable Retention Force                | 22kg to 44kg (50lb to 100lb) - Dependent on cable material and diameter.                     |
|                                   | Cable O.D. - Standard Jaw                    | 3mm to 7mm (0.118" to 0.275")  |
|                                   | Cable O.D. - Large Jaw                       | 6mm to 8mm (0.236" to 0.314")  |
| <b>MATERIALS</b>                  | Connector Shell Material                     | Diecast Zinc Alloy EZDA No.3   |
|                                   | Shell Finish                                 | Satin Nickel or Black Polyester  |
|                                   | Insulators                                   | UL94 V-0 PBT Resin or Modified PPE Resin - Black   |
|                                   | Boot / Backshell                             | UL94 V-0 PBT Resin or Modified PPE Resin - Black or Metal CuZn <sup>39</sup> Pb <sup>3</sup> |
|                                   | Finish                                       | Satin Nickel or Black  |
|                                   | Cable Clamp                                  | UL94 V-0 PBT Modified PPO Resin - Black  |
|                                   | Cable Bushing                                | Thermoplastic Polyurethane   |
|                                   | Contacts / Plating                           | Brass /Ag or Au over 2µm Ni  |


<sup>1)</sup> Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.



## PART NUMBER BREAKDOWN


### T-SERIES (PRO RANGE)

E. G. **TS3PBMJ-AU BULK**  
**T** (Series Prefix), **S3**(Stereo), **Plug Black**, **Metal Nut (Black)**, **J** (Large Jaws),  
**- AU** (Gold Plated Contacts), **Bulk** Packaged.



|                              |       |   |   |
|------------------------------|-------|---|---|
| <b>SERIES PREFIX</b>         | T     | = | Series Prefix   |
| <b>CONTACT TYPE</b>          | M2    | = | 2 Pole (mono)   |
|                              | S3    | = | 3 Pole, tip/ring/sleeve (stereo)                        |
| <b>SHELL TYPE AND FINISH</b> | P     | = | Plug Satin Nickel                                       |
|                              | PB    | = | Plug Matt Black   |
| <b>BACKSHELL TYPE</b>        | Blank | = | Plastic Nut   |
|                              | M     | = | Metal Nut - Black                                       |
|                              | N     | = | Metal Nut - Satin Nickel                                |
| <b>CABLE CLAMP</b>           | Blank | = | Standard Jaws 3.0-6.5 mm<br>Cable OD (.118"Ø to .250"Ø) |
|                              | J     | = | Large Jaws 6.5 - 8.0 mm<br>Cable OD (.250"Ø to .314"Ø)  |
| <b>CONTACT PLATING</b>       | Blank | = | Standard Plating (Standard)                             |
|                              | AU    | = | Gold Plated Contacts                                    |
| <b>PACKAGING</b>             | Blank | = | Individual Bags   |
|                              | BULK  | = | Bulk Packed   |

### ISO VIEW OF TM2P





**Features:**

- Mono or Stereo (TRS).
- Stylish shell design.
- Robust diecast shell in Satin nickel or Black finish.
- Gold plated contact tip.
- Flexible grommet cable protection.
- Improved solderability.
- Precision machined contacts.
- Convenient bulk packaging.

**Options:** Black Shell.

| PRODUCT - FIGURE | DRAWING | Dimensions in mm (inches) | DESCRIPTION   | VARIATIONS     | PART NUMBER                      |
|------------------|---------|---------------------------|---|----------------|----------------------------------|
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Diecast Shell, Satin finish, Gold plated tip, Flexible grommet. | Mono<br>Stereo | ACPM-GN-AU<br>ACPS-GN-AU         |
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Diecast Shell, Black finish, Gold plated tip, Flexible grommet. | Mono<br>Stereo | ACPM-GB-AU<br>ACPS-GB-AU         |
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Machined compact shell, Nickel finish.                          | Mono<br>Stereo | ACPM - CN<br>ACPS - CN           |
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Machined compact shell, Gold finish.                            | Mono<br>Stereo | ACPM - CG - AU<br>ACPS - CG - AU |
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Machined shell, Nickel finish.                                  | Mono<br>Stereo | ACPM - MN<br>ACPS - MN           |
|                  |         |                           | 1/4" (6.35mmø)<br>Phone plug, Diecast shell, Nickel finish, Gold plated tip.                  | Mono<br>Stereo | ACPM- ZN - AU<br>ACPS- ZN - AU   |







| PRODUCT - FIGURE | DRAWING<br>Dimensions in mm (inches) | DESCRIPTION  | TYPE   | PART NUMBER |
|------------------|--------------------------------------|--|--------|-------------|
|                  |                                      | 1/4" (6.35mmø)<br>Jack, Vertical PCB<br>mount, Metal nut and<br>insert | Mono   | ACJM-MV     |
|                  |                                      | 1/4" (6.35mmø)<br>Jack, Vertical PCB<br>mount, Metal nut and<br>insert | Stereo | ACJS-MV     |
|                  |                                      | 1/4" (6.35mmø)<br>Jack, Solder lugs,<br>Metal nut and insert           | Mono   | ACJM-MS     |
|                  |                                      | 1/4" (6.35mmø)<br>Jack, Solder lugs,<br>Metal nut and insert           | Stereo | ACJS-MS     |



## PANEL CUTOUTS -FRONT VIEW



## PCB FOOTPRINT - CONNECTOR SIDE OF PCB

ACJM-MV  
ACJS-MV  
ACJM-MS  
ACJS-MS





ACJM-MV  
ACJS-MV

ACJM-PH  
ACJM-MH  
ACJS-PH  
ACJS-MH  
ACJM-PC  
ACJM-MC  
ACJS-PC  
ACJS-MC





ACJM-PH  
ACJM-MH  
ACJS-PH  
ACJS-MH  
ACJM-PC  
ACJM-MC  
ACJS-PC  
ACJS-MC

ACJM-MHD  
ACJS-MHD



ACJM-MHD  
ACJS-MHD

ACJM-MHDR  
ACJS-MHDR



ACJM-MHDR  
ACJS-MHDR