



THIS DOCUMENT CONTAINS DATA PROPRIETARY  
TO PROJECTS UNLIMITED, INC. ANY USE OR  
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR  
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.  
IS PROHIBITED.  
© 2003, Projects Unlimited Inc.

## SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.1	W
MAX INPUT POWER	0.3	W
IMPEDANCE	8±20%	OHM
OUTPUT SPL @ 0.89Vrms/0.1M (AT 1.0 kHz)	80	dBA
DISTORTION	5%	—
RESONANT FREQUENCY	1,000±200	Hz
FREQUENCY RANGE	1,000 ~ 10,000	Hz
HOUSING MATERIAL	NYLON	—
CONE MATERIAL	PET	—
MAGNET MATERIAL	ALNICO	—
OPERATING TEMPERATURE	-50 ~ +70	°C
WEIGHT	25	grams



### NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE  
OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME  
AT-261.DWG

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/13/02	
A	REVISED TO NEW TEMPLATE	2/5/04	R. W.
B	REVISED DIMENSION SIZE AND STYLE	02/16/06	B. R.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN  
MILLIMETERS, TOLERANCES ARE ±0.5 AND  
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN RABL	5/02
APPROVED S.J.	5/02
DO NOT SCALE DRAWING	

projects ®  
unlimited

Dayton, Ohio

## SPEAKER TRANSDUCER

SIZE	DRAWING NO.
A	AT-261
SCALE: N.T.S.	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-261](#)