



Specifications:

Current rating : 3A, 250V.

Surge Protection Data:

Voltage : 220V to 240V.
Maximum operating voltage : 300V ac (rms).
Mains three way protection : LN LE NE.
Peak current : 4.5kA.
Maximum energy : 3 x 125J.
Maximum clamping voltage : 775 volts.
Response time : <50ns.

Standard:

BS 1363/A; BS5733/A

Conditions for Use:

An ambient temperature in the range -5°C to +40°C, the average value over 24 hours not exceeding 25°C.

A situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits specified in a).

An altitude not exceeding 2000 metres above sea level.

An atmosphere no subject to abnormal pollution by smoke, chemical fumes, rain, spray, prolonged periods of high humidity or other abnormal conditions.

Safety Specifications

Item	Conditions	Requirements
Appearance	-	No defect such as cracks, deep scratches or blemishes
Marking	-	Shall be legible and must be clear
Insulation resistance	500 + 250Vdc 1 minute	Shall not be less than 5MΩ
Dielectric strength	2000 ±60V 1 minute	No damage or breakdown
Resistance to aging	70° ±5° 168 hours	No cracks or become sticky
Construction	20° ±5°	Complied with figure 11, 12, 14, 16 gauge
Torque test	Value of 0.6Nm (6.1kgf/cm)	Terminal, cord grip and cover screws shall withstand the torque applied
Glow wire test	650°/750° electrically heated	Flame must extinguish within 30 seconds.
Temperature rise	14A, 250V	Temperature rise must not exceed: 1. Terminals or terminations : 52K 2. Accessible surface : 52K

Safety Specifications

Item	Conditions	Requirements
Make and break test of switch	13A, 250V, 15,000 times	Voltage drop across each switched pole shall not exceed 75mV
Drop test	Fit with 3G1.25mm ² cable, 2.25m and drop at a height of 0.4m above the floor	No external damage which might affect safety and no components shall have become detached
Live parts accessibility	Subjected to 1.0mm test probe with applied force of 5N when they are mounted and wired as in normal use	Live parts of socket shall not be accessible

Construction

Item	Description	Material
1	Socket base and cover	FRPP
2	Conductors (bus bar)	Brass
3	Cover Screw	Mild steel nickel plated
4	Switch	Nylon house with brass terminals
5	Shutter	Nylon (PA)
6	Spring	Mild steel
7	Neon lamp with 220k Ω resistor	Orange light
8	Neon lamp cover	Polycarbonate (PC)
9	Switch Rocker	Polycarbonate (PC)
10	Surge component	Metal oxide varistor + thermal fuse + neon indicator (if applicable)
11	Plug	13A BS 1363 plug
12	Cable	PVC, BS6500 3 x 1.25mm ²

Part Number Table

Description	Part Number
Extension Lead, 4 Gang, NDIV-SW, 2M	2814S
Extension Lead, 6 Gang, NDIV-SW, 2M	2816SP
Extension Lead, 8 Gang, NDIV-SW, 2M	2818SP

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Elec is the registered trademark of the Group. © Premier Farnell plc 2009.