


Electromagnetic Transducers



- QMX range are Compact transducers with removable sealing label to allow washing after dip soldering
- QMB is an ultra thin compact transducer that is NOT washable

Order Code	119-3534	119-3535	119-3540
Mfrs List No.	QMX-05	QMX-12	QMB-105P
Frequency	2400Hz	2400Hz	2048Hz
Rated Voltage (50% duty cycle square wave)	5V	12V	1.5V
Current consumption (Typ)	33mA	28mA	9.1mA
Coil Resistance	47Ω	140Ω	50Ω
Coil Impedance	80Ω	240Ω	140Ω
Sound Output (min @ 10cm)	85dB	85dB	70dB
Operating Temperature	-40°C to +85°C	-40°C to +85°C	-20°C to +60°C
Weight	2g	2g	2g
Dimensions - DiaxHxPin PitchxDia	12 x 9 x 6.5 x 0.6		12 x 5.4 x 6.5 x 0.6

212930.473263

Order Code	Price Each	
119-3534●		+
119-3535●		
119-3540●		