

Keyword:
Extended Temperature Range

Type: **SL-560**

Performance Data **Size AA**
(Typical values for batteries stored at 25 °C for one year)


System	Li/SOCl ₂
Nominal voltage	3.6 V
Nominal capacity	1.7 Ah
Nominal current	2 mA
Max. continuous discharge current	20 mA
Anode surface area	14 cm ²
Lithium content	0.65 g
Weight	18 g
Volume	8.0 cm ³
Temperature range	-55...+130 °C

WARNING:
Fire, explosion, and severe burn hazard. Do not recharge, disassemble, heat above 150 °C, incinerate, or expose contents to water.


UL recognition under file MH 12827

See also our website under Products/Safety



Typical Discharge Curves at +85 °C



Available Capacity



Operating Voltage



Available Terminations

SL-560/S	Standard
SL-560/T	Tags
SL-560/P	Pins
SL-560/PR	Pins Radial
SL-560/PT	Polarized Tags

Catalogue No.

11 1 05601 00
11 1 05602 00
11 1 05603 00
11 1 05606 00
11 1 05608 00

Any values given here are for information purposes only. They also depend on actual conditions of use and are not warranties of future performance. Subject to change.