



TECHNICAL SPECIFICATIONS

Material:	Zinc, Nickel Plated Brass Ferrule / Brass Ring
Operating Temperature:	-40°C to +120°C
Cable Entry:	Top Entry
Thumbscrews:	UNC 4-40 (Standard) M2,5 or M3 on request
Cable O.D.:	Up to 9,5mm
Accessories:	See page 190-194
Assembly Instruction:	See page 201




Features:

- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Re-openable
- Strain relief inserts ensure a secure termination
- Full Metal Jackscrew as standard



Max Cable O.D. (mm)	Body: Dy / Di	Ring: Dy / Di	Order Code X :
6,0	5,0 / 4,0	7,0 / 6,0	1
7,5	7,0 / 6,0	9,0 / 8,0	2
8,5	8,0 / 7,0	10,0 / 9,0	3
9,5	9,0 / 8,0	11,0 / 10,0	4



Size MHDZK	Dim A	Dim B	Dim C
9-way	31,2	39,9	15,0
15-way	39,5	41,5	15,0
25-way	53,4	48,6	15,0
37-way	69,7	53,6	15,0

Ordering information:

Size:	P/N - Kitted:	Product Code:
9-way	6560-06 X 5-01	DTZK09-CZK-K
15-way	6560-06 X 5-02	DTZK15-CZK-K
25-way	6560-06 X 5-03	DTZK25-CZK-K
37-way	6560-06 X 5-04	DTZK37-CZK-K

Size:	P/N - BULK:	Product Code:
9-way	6561-06 X 5-01	DTZK09-CZK
15-way	6561-06 X 5-02	DTZK15-CZK
25-way	6561-06 X 5-03	DTZK25-CZK
37-way	6561-06 X 5-04	DTZK37-CZK

Example:	(Size 15 with 7,5mm Ferrule Kit)
6560-06 2 5-02	DTZK15-CZK-K