

FED. MFG. CODE 91929


(RIGHT HAND)

M **BAF1-2RN-RH** (RIGHT HAND)
 CATALOG LISTING
 ISSUE 16
 PAGE 1 OF 1

REVISIONS	
A	C073751
MAM	
15 OCT 92	
B	CO- 77179B
K D R	
21 FEB 94	
C	C073287M
J A F	
8 MAY 95	

DDM/CAD
DRAWN

	CHECK	WLS	160CT92	CHECK	CHECK	RELEASE NO.	REPLACES
NAM	150CT92						
	150CT92	WLS	160CT92				



CHARACTERISTICS									
OPERATING FORCE	—	—	—	2 1/2 LBS	MAX				
RELEASE FORCE	—	—	—	1/2 LB	MIN				
DIFFERENTIAL TRAVEL	—	—	—	.010	MAX				
OVERTRAVEL	—	—	—	.219	MIN				
BASIC SWITCH REPLACEMENT	—	—	—						
				BA-2R708-P7					

ELECTRICAL DATA	
CONTACT ARRANGEMENT	
S P D T	
L23	20A 125, <u>250</u> OR 480 VAC 10A 125 VAC "L" 1HP 125 VAC, 2HP <u>250</u> VAC 1/2A 125 VDC, 1/4A 250 VDC



SCALE	FULL
-------	------

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT	.500 LB
--------	---------

1 - 8-32 UNC X (.219) BINDER HEAD TERMINAL SCREWS AND CUPWASHERS

ANSI Y14.5M-1982 APPLIES