







EM-121064-727



NOTES

- PLEASE SEE SHEETS 2-5 FOR CURRENTLY CONFIGURED PART NUMBERS. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
- EARTH POSITION SHOWN, H12.
- FOR PACKAGING SEE PACKAGING SPEC PK-121064-S18
- PRODUCT SPEC: SEE PS-121201-001

LAST INSPECTION NUMBER 2



ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	PCB
4	INSERT ASSEMBLY
5	GASKET

S18309TA122**

SERIES

S18= INTERNAL THREAD FORM A

POLES

2= 2 POLE & 3= 3 POLE

THREAD

09= PG9, 11= PG11, M6=M16x1.5, M0= M20x1.5, 12= 1/2" GAS 13= 1/2" NPTF

MATERIAL AND HOUSING COLOUR

G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= PA12 TRANSPARENT,

B= PA6 WHITE

CIRCUIT

SEE DETAILS IN CATALOGUE

VOLTAGE

SEE DETAILS IN CATALOGUE

SCREW AND GASKET

1= NBR PROFILE GASKET & SCREW

2= NBR FLAT GASKET & SCREW

3= WHITE SILICON PROFILE GASKET & SCREW

4= WHITE SILICON FLAT GASKET & SCREW

A= NBR PROFILE GASKET & SCREW +2mm

B= NBR FLAT GASKET & SCREW +2mm

NON STANDARD COMPONENTS

14= PACKED IN NEUTRAL BAG

23= FULLY MOUNTED

54= WITH PIN 3 AS EARTH

65= SPECIAL GROMMET

67= NEUTRAL PACKAGING

84= TAMPO PRINTING ON DIODE

3F= 24DC W/O TAMPO PRINTING

5J= BOXES OF 100

5N= PACKED IN BOXES OF 200

6U= GI BY500-800 DIODE

AF= CENTRE SCREW MOUNTED

AG= DIODE IN4948

P7= IP67 COMPLIANT

SA= UL LISTED PART

ADDED PART NUMBER	EC NO: IPG2016-1371	DRWN:BCAFFREY 2016/04/11	CHKD:DMAHER 2016/04/12	APPR:STGRIFFIN 2016/04/18	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
										MM ONLY	1.5:1	METRIC				
								▽=0	4 PLACES ± ---	± ---	DRAWN BY	DATE	TITLE			
								▽=0	3 PLACES ± ---	± ---	JOCONNOR	2011/05/13				
									2 PLACES ± 0.1	± ---	CHECKED BY	DATE	S18 SERIES INTERNAL THREAD			
	1 PLACE ± 0.2	± ---	DMAHER	2011/05/16												
								ANGULAR ± ---°		APPROVED BY	DATE	MOLEX MOLEX INCORPORATED				
										EFOLAN	2011/06/07					
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
										SEE SHEETS 2, 3, 4 & 5		SD-121064-002		1 OF 5		
										SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
								A2								

[illegible]

PART No.	mPm PART No.	DESCRIPTION	CIRCUIT	VOLTAGE	INDICATOR
1210641368	S18209TC3G4	TYPE A 2P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C3	12V	AMBER LED
1210641455	S18209TC321P7	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IP67 COMPLIANT	C3	24V	RED LED/LAMP
1210641510	S182M6TC312	TYPE A 2P M16x1.5 TRANSPARENT, NBR FLAT GASKET & SCREW	C3	12V	RED LED/LAMP
1210641624	S182M6TC3D4	TYPE A 2P M16x1.5 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C3	115V	GREEN LED
1210641626	S18209TC3B3	TYPE A 2P PG9 TRANSPARENT, WHITE SILICON PROFILE GASKET & SCREW	C3	24V	GREEN LED
1210641670	S18211TC32114	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW, IN NEUTRAL BAG	C3	24V	RED LED/LAMP
1210641697	S18209TC311P7	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IP67 COMPLIANT	C3	12V	RED LED/LAMP
1210641721	S18211TC3D1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	115V	GREEN LED
1210641733	S18209TC321AF	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, WITH SCREW MOUNTED	C3	24V	RED LED/LAMP
1210641741	S18211TC322	TYPE A 2P PG11 TRANSPARENT, NBR FLAT GASKET & SCREW	C3	24V	RED LED/LAMP
1210641756	S182M6TC321	TYPE A 2P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	24V	RED LED/LAMP
1210650200	S18209TC32165	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, WITH SPECIAL GROMMET	C3	24V	RED LED/LAMP
1210640727	S18309TA122	TYPE A 3P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	A1	24V	RED LED/LAMP
1210640717	S18309NE051	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210640718	S18309NE151	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	E1	230V	RED LED/LAMP
1210640720	S18309NE651	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	E6	230V	RED LED/LAMP
1210640725	S18309TA051	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	A0	230V	RED LED/LAMP
1210640759	S18311TA121	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	24V	RED LED/LAMP
1210641420	S183M6TA121	TYPE A 3P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	24V	RED LED/LAMP
1210640730	S18309TA151	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	230V	RED LED/LAMP
1210640731	S18309TA1B1	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	24V	GREEN LED
1210640736	S18309TC321	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	24V	RED LED/LAMP
1210640737	S18309TC322	TYPE A 3P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	C3	24V	RED LED/LAMP
1210640744	S18309TC441	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	RED LED/LAMP
1210640742	S18309TC421	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210640743	S18309TC424	TYPE A 3P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C4	24V	RED LED/LAMP
1210640768	S18311TC441	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	RED LED/LAMP
1210640747	S18309TC521	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C5	24V	RED LED/LAMP
1210640755	S18309TS0B1	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	S0	24V	GREEN LED
1210640766	S18311TC3H1	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	24V	AMBER LED
1210640764	S18311TC321	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	24V	RED LED/LAMP
1210641250	S18309TC314	TYPE A 3P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C3	12V	RED LED/LAMP
1210640767	S18311TC421	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210650502	S18209TC3G465	TYPE A 2P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW, WITH SPECIAL GROMMET	C3	12V	AMBER LED
1210640761	S18311TA151	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	230V	RED LED/LAMP
1210640578	S18209TC411	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	12V	RED LED/LAMP
1210640579	S18209TC421	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210640581	S18209TC422	TYPE A 2P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	C4	24V	RED LED/LAMP
1210640583	S18209TC431	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	48V	RED LED/LAMP
1210640588	S18209TC442	TYPE A 2P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	C4	115V	RED LED/LAMP
1210640590	S18209TC451	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	230V	RED LED/LAMP
1210640592	S18209TC452	TYPE A 2P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	C4	230V	RED LED/LAMP
1210640593	S18209TC4A1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	12V	GREEN LED
1210640594	S18209TC4B1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	GREEN LED
1210640596	S18209TC4C1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	48V	GREEN LED
1210640600	S18209TC4H1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	AMBER LED
1210641706	S183M6TA151	TYPE A 3P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	230V	

SEE SHEET ONE EC NO: IPG2016-1371 DRWN:BCAFFREY 2016/04/11 CHKD:DMAHER 2016/04/12 APPR:STGRFFIN 2016/04/18 AC	DESCRIPTION REV	QUALITY SYMBOLS ▼=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY JOCONNOR	DATE 2011/05/13	S18 SERIES INTERNAL THREAD				
			4 PLACES	± ---	± ---	CHECKED BY DMAHER	DATE 2011/05/16					
			3 PLACES	± ---	± ---	APPROVED BY EFOLAN	DATE 2011/06/07	MOLEX MOLEX INCORPORATED				
			ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-121064-002		3 OF 5					
			SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J														J
I														I
H														H
G														G
F														F
E														E
D														D
C														C
B														B
A														A

PART No.	mPm PART No.	DESCRIPTION	CIRCUIT	VOLTAGE	INDICATOR
1210641371	S183M6TC321	TYPE A 3P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C3	24V	RED LED/LAMP
1210640681	S18211TC451	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	230V	RED LED/LAMP
1210640685	S18211TC4H1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	AMBER LED
1210640686	S18211TC4L1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	AMBER LED
1210640687	S18211TC4M1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	230V	AMBER LED
1210640716	S18309ND011	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	12V	DIODE
1210640710	S18213TC421	TYPE A 2P 1/2" NPT,F TRANSPARENT NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210640711	S18213TC441	TYPE A 2P 1/2" NPTF, TRANSPARENT NBR PROFILE GASKET & SCREW	C4	115V	RED LED/LAMP
1210641268	S182M6TC421	TYPE A 2P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210640741	S18309TC414	TYPE A 3P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C4	12V	RED LED/LAMP
1210641309	S18209TC42A	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW +2mm	C4	24V	RED LED/LAMP
1210641317	S18209TC4G1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	12V	AMBER LED
1210641494	S18309TC422	TYPE A 3P PG9 TRANSPARENT, NBR FLAT GASKET & SCREW	C4	24V	RED LED/LAMP
1210641341	S18211TC4D1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	GREEN LED
1210641374	S182M6TC4H1	TYPE A 2P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	AMBER LED
1210641387	S18209TC424	TYPE A 2P PG9 TRANSPARENT, WHITE SILICON FLAT GASKET & SCREW	C4	24V	RED LED/LAMP
1210650474	S18309TA1H154	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW WITH PIN 3 AS EARTH PIN	A1	24V	AMBER LED
1210641423	S18211TC4B1	TYPE A 2P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	GREEN LED
1210641517	S18309ND021	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	24V	DIODE
1210641498	S182M6TC422	TYPE A 2P M16x1.5 TRANSPARENT, NBR FLAT GASKET & SCREW	C4	24V	RED LED/LAMP
1210641548	S18309ND041	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	115V	DIODE
1210641560	S182M0TC421	TYPE A 2P M20x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	RED LED/LAMP
1210641561	S182M0TC441	TYPE A 2P M20x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	RED LED/LAMP
1210641627	S18211TC443	TYPE A 2P PG11 TRANSPARENT, WHITE SILICON PROFILE GASKET & SCREW	C4	115V	RED LED/LAMP
1210641588	S18309NE05167	TYPE A 3P PG9 BLACK, NBR PROFILE GASKET & SCREW, IN NEUTRAL PACKAGING	E0	230V	DIODE
1210641650	S182M0TC4B1	TYPE A 2P M20x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	24V	GREEN LED
1210641669	S18209TC42114	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW IN NEUTRAL BAG	C4	24V	RED LED/LAMP
1210641749	S18209TC4C1	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	48V	GREEN LED
1210641753	S182M6TC4L1	TYPE A 2P M16x1.5 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	115V	AMBER LED
1210650207	S18209TC4215J	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IN BOXES OF 100	C4	24V	RED LED/LAMP
1210650208	S18209TC42165	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, WITH SPECIAL GROMMET	C4	24V	RED LED/LAMP
1210650213	S18209TC4415J	TYPE A 2P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IN BOXES OF 100	C4	115V	RED LED/LAMP
1210640510	S18209GD011	TYPE A 2P PG9 GRAY, NBR PROFILE GASKET & SCREW	D0	12V	DIODE
1210640512	S18209GD031	TYPE A 2P PG9 GRAY, NBR PROFILE GASKET & SCREW	D0	48V	DIODE
1210641684	S18309NE052	TYPE A 3P PG9 BLACK, NBR FLAT GASKET & SCREW	E0	230V	DIODE
1210640513	S18209GD041	TYPE A 2P PG9 GRAY, NBR PROFILE GASKET & SCREW	D0	115V	DIODE
1210640517	S18209ND011	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	12V	DIODE
1210640518	S18209ND021	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	24V	DIODE
1210640519	S18209ND022	TYPE A 2P PG9 BLACK, NBR FLAT GASKET & SCREW	D0	24V	DIODE
1210641447	S18309TC411	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	12V	RED LED/LAMP
1210640521	S18209ND032	TYPE A 2P PG9 BLACK, NBR FLAT GASKET & SCREW	D0	48V	DIODE
1210640522	S18209ND041	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	115V	DIODE
1210640523	S18209ND051	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW	D0	230V	DIODE
1210641717	S18309TA1C1	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW	A1	48V	GREEN LED
1210640515	S18209GE051	TYPE A 2P PG9 GRAY, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210640524	S18209NE051	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210641735	S18309TC3B114	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IN NEUTRAL BAG	C3	24V	GREEN LED
1210640613	S18209WE051	TYPE A 2P PG9 BLACK V0, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210640628	S18211GE051	TYPE A 2P PG11 GRAY, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210641744	S18309TC32114	TYPE A 3P PG9 TRANSPARENT, NBR PROFILE GASKET & SCREW, IN NEUTRAL BAG	C3	24V	RED LED/LAMP
1210640769	S18311TC451	TYPE A 3P PG11 TRANSPARENT, NBR PROFILE GASKET & SCREW	C4	230V	RED LED/LAMP
1210640632	S18211NE051	TYPE A 2P PG11 BLACK, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210640694	S18212NE051	TYPE A 2P 1/2" GAS BLACK, NBR PROFILE GASKET & SCREW	E0	230V	DIODE
1210641334	S18209NE05165	TYPE A 2P PG9 BLACK, NBR PROFILE GASKET & SCREW, WITH SPECIAL GROMMET	E0	230V	DIODE
1210641547	S18209WE05A	TYPE A 2P PG9 BLACK V0, NBR PROFILE GASKET & SCREW +2mm	E0	230V	DIODE

SEE SHEET ONE

EC NO: IP02016-1371

DRWN:BCAFFREY 2016/04/11

CHKD:DMAHER 2016/04/12

APPR:STGRIFFIN 2016/04/18

REV

DESCRIPTION

▽=0

▽=0

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± ---

2 PLACES ± 0.1 ± ---

1 PLACE ± 0.2 ± ---

ANGULAR ± ---°

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY

JOCONNOR

DATE

2011/05/13

CHECKED BY

DMAHER

DATE

2011/05/16

APPROVED BY

EFOLAN

DATE

2011/06/07

MATERIAL NO.

SEE CHART

SCALE

1.5:1

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

S18 SERIES
INTERNAL THREAD

MOLEX INCORPORATED

DOCUMENT NO.

SD-121064-002

SHEET NO.

4 OF 5

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SEE SHEET ONE EC NO: IPG2016-1371 DRAWN BY: JACAFFREY CHK'D BY: DMAHER APPR: STGRIFIN 2016/04/11 2016/04/12 2016/04/18	QUALITY SYMBOLS ▼=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 		
				mm	INCH	DRAWN BY DATE JOCONNOR 2011/05/13		TITLE S18 SERIES INTERNAL THREAD			
			4 PLACES	± ---	± ---	CHECKED BY DATE DMAHER 2011/05/16		MOLEX MOLEX INCORPORATED			
			3 PLACES	± ---	± ---	APPROVED BY DATE EFOLAN 2011/06/07					
			2 PLACES	± 0.1	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
			1 PLACE	± 0.2	± ---	SEE CHART		SD-121064-002		5 OF 5	
			ANGULAR ± ---°		SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
AC		REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								