

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370111](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Non-NEMA Duplex Receptacles, Cord Clamp, Duplex Cover Plates, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, LNEMA 5-15 Plug

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR6837
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	N/A
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Watertite Wet-Location Wiring Solutions
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	Multiple Outlet Box
UPC	78678874117
Physical	
Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	15.24m (50.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton
Electrical	
Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	125V
Material Info	
Engineering Number	3000-8B143



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130137](#) Series