


CODICE FORNITORE "A 047"
(SUPPLIER CODE "A 047")

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)


METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)




PER DETTAGLIO POLARIZZAZIONI VEDERE FOGLIO 2 DI 3
PER P/NS CONTROPARTI PORTAMASCHI, VEDERE TABELLA.
(FOR POLARIZATION DETAIL SEE SHEET 2 OF 3, FOR
COUNTERPART CAP HSG. P/NS SEE THE TABLE).

NO. DI IMPRONTA STAMPO
(MOULD CAVITY IDENTIF. NO.)



SEZIONE A-A
(SECTION A-A)



NUM. DI CAVITA'
(CIRCUIT IDENTIF. NO.)

CAVITA' ADATTE PER CONTATTI P/N:
(CAVITIES SUITABLE FOR CONTACTS P/N:)
282374-1 SEZ. 0.3-0.5 mm² (COD. FIAT 1/23197/44)
282375-1 SEZ. 0.75-1.5 mm² (COD. FIAT 1/24834/44)

282525-8 VERS. VERTICALE (VERTICAL VERS.)	282371-4	GRIGIO (GREY)	PBT (PBT UNFILLED)	282367-4
282525-7 VERS. VERTICALE (VERTICAL VERS.)	282371-3	BLU (BLUE)		282367-3
282525-6 VERS. VERTICALE (VERTICAL VERS.)	282371-2	NERO (BLACK)		282367-2
282629-1 VERS. ORIZZONTALE (HORIZONTAL VERS.) 282525-5 VERS. VERTICALE (VERTICAL VERS.)	282371-1	BIANCO (NATURAL)		282367-1
CONTROP. P.C.B. (HEADER ASSY)	PORTAMASCHI VOLANTE (CAP HOUSING)	COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO
(TOLERANCES: UNLESS OTHERWISE SPECIFIED)

± 0.3

± 2°

ANGOLI (ANGLES)

DIS. M. PALMA

CONTR. C. TARTARI

DESCRIZIONE (DESCRIPTION)
CONN. PLUG HOUSING 12 POSITION
(PORTAFEMMINE) DOUBLE ROW


LOC. SIZE NUMERO (DWG NO.)

REV. FOGLIO (SHEET) 1 DI 3


1) PER RAPPRESENTAZIONE DIMA CONTROPARTE VEDERE FOGLIO 3 DI 3.
(FOR COUNTERPART DETAIL SEE SHEET 3 OF 3).

2) QUOTA VALIDA SOLO PER VERSIONE 282367-1.
(VALID DIMENSION ONLY FOR 282367-1 VERSION)

DISTRIBUZIONE
(PRINT DIST.)



—ASSE CAVITA'
(CAVITY AXIS)



REV. (REV. 1, 19, 3)	REVISION (REVISION RECORD)	DIS. (DR)	DA (DA)
-------------------------	-------------------------------	--------------	------------

AMP-ITA 7523 - 5/82

SEZIONE C-C
(SECTION C-C)

SEZIONE A-A
(SECTION A-A)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)


METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

SEZIONE B-B
(SECTION B-B)

SEZIONE G-G
(SECTION G-G)

SEZIONE F-F
(SECTION F-F)



COLORE (COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		19	
THIS DRAWING IS UNPUBLISHED				RELEASE FOR PUBLICATION	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
0 DEC. PLACE ±0.3 1 DEC. PLACE ±0.1 2 DEC. PLACE ±0.05				SCALA (SCALE) 2:1	
ANGOLI (ANGLES) 0° 30'		TE Connectivity			
DIS. (DR.)		DESCRIZIONE (DESCRIPTION) 070 SERIES MULTILOCK* CONN. PLUG HOUSING 12 POSITION (DIMA DI MONTAGGIO)			
CONT. (CHK)		LOC. SIZE NUMERO (DWG NO)		REV. FOGLIO (SHEET)	
APP. (APP.)		I A3 C-282367		02 3 DI (OF) 3	
REV. (REV.)		REVISIONI (REVISION RECORD)		DIS. DATA (DR. DATE)	

DISTRIBUZIONE
(PRINT DIST.)