





MOUNTING DATA FOR THE ACCESSORIES

NYLON CAP NUTS	Mounting hole mm (min)	Max chassis thickness (mm)	Width of jaws (mm)	Creepage distance (mm)	Test voltage 50–60 Hz 1 min (KVAC)	Max tightening torque (NM)	Capacitor diameter (mm)
 PYB 7033, M8	Ø 17.5	5	17	4.5	2.5	3	Ø = 35
 PYB 7026, M12	Ø 17.5	5	19	2.5	2,5	8	Ø > 35
 PYB 7041, M12	Ø 22.5	5	19	5	2.5	8	Ø > 35
 PYB 7042, M12	Ø 30.5	5	19	9	4	8	Ø > 35