

# Edison base plug fuses – dual-element, time-delay, 125 volts, up to 30 amps



## Catalog symbol:

- T - (amps)
- BP/T - (amps)

## Description:

Bussmann® series dual-element, time-delay Edison style plug fuse.

## Specifications:

### Ratings

- Volts — 125 Vac or less
- Amps — 3/10 to 30 A
- Interrupting rating — 10 kA RMS Sym

### Agency Information

- UL® Listed (up to 6-1/4 A), Std. 248-11, Guide JFHR, File E56412, (7 to 30 A) Guide JEFV, File E12112
- CSA® Certified, Class 1423-01, File 53787
- CE

### Catalog numbers (amps)

|            |            |        |
|------------|------------|--------|
| T - 3/10   | T - 2-1/4  | T - 7  |
| T - 4/10   | T - 2-1/2  | T - 8  |
| T - 1/2    | T - 2-8/10 | T - 9  |
| T - 6/10   | T - 3      | T - 10 |
| T - 8/10   | T - 3-2/10 | T - 12 |
| T - 1      | T - 3-1/2  | T - 14 |
| T - 1-1/8  | T - 4      | T - 15 |
| T - 1-1/4  | T - 4-1/2  | T - 20 |
| T - 1-4/10 | T - 5      | T - 25 |
| T - 1-6/10 | T - 5-6/10 | T - 30 |
| T - 1-8/10 | T - 6      | —      |
| T - 2      | T - 6-1/4  | —      |

## Recommended fuse holders

| Catalog numbers | Type box     | Catalog numbers | Type box    |
|-----------------|--------------|-----------------|-------------|
| SOU             | 2 1/4" handy | SOY             | 4" square   |
| SRU             |              | SRY             |             |
| SSU             |              | SSY             |             |
| SOW             | 2 3/4" handy | SSY-RL          |             |
| SRW             |              | STY             |             |
| SSW             |              | SCY             |             |
| SOX             | 4" octagon   | SOY-B           | Single gang |
| SRX             |              | SSN             |             |


## Package quantity and weight

| Amp ratings  | Quantity |          | Weight  |             |
|--------------|----------|----------|---------|-------------|
|              | Per box  | Per card | Per box | Per 5 cards |
| 3/10 to 14 A | 4        | 1        | 0.210   | 0.46        |
| 15 to 30 A   | 4        | 3        | 0.25    | 1.07        |

## Features:

- Heavy duty time-delay plug fuse
- Use to protect critical motor circuits or motors that cycle on/off frequently
- An industrial/commercial grade product with exclusive dualelement construction
- Edison base size
- These fuses thread into fuse receptacles and box cover units
- Industrial strength, featuring an exclusive dual-element construction
- This spring loaded design provides superior short circuit and overload protection
- More time-delay than the medium duty Type TL fuses in order to better protect industrial motors and critical residential circuits

**Time-current curve – average melt**



The only controlled copy of this Data Sheet is the electronic read-only version located on the Eaton Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2016 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 1034 – SB98107  
May 2016

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.  
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[T-25](#) [T-1-6/10](#) [T-3/10](#) [T-6/10](#) [T-1/2](#) [T-30](#) [T-15](#) [T-12](#) [T-1-4/10](#) [T-20](#) [T-14](#) [T-1-1/8](#) [T-8/10](#) [T-3-1/2](#) [T-4-1/2](#) [T-4/10](#) [BP/T-30](#) [BP/T-20](#) [BP/T-15](#) [BP/T-10](#) [BP/T-12](#) [BP/T-25](#)