

5




4

3

2

1

(1:1)



SW13


width across flats 13

SW17

width across flats 17

X

Steckgesicht n.
Contact face acc.to
IEC 61076-2-101



Leiterquerschnitt conductor cross section	0,14 - 0,34mm ² AWG26-AWG22
Kabeldurchmesser cable outside diameter	4,5 - 8,8mm

 ALL Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maße/ Free size tolerances	
				Dat.	Name	Maßstab/Scale 2:1	M12-L RSV geschirmt, 4-polig, Stift, D-kodiert Circular connector shielded, 4-pole, male, D-coded
EC01527	01.07.11	DY	Detail.	21.05.03	Grie		
413867	13.05.08	DY	Insp.		Sr		
412800	19.03.07	DY	Stand.				
411606	08.08.05	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 21 03 281 1405
410925	10.03.04	DY					
Mod.	Dat.	Name				Sub.	Blatt/ page

