

**(2.54 mm) .100"****BBS, BBL, BHS, BBD, BDL SERIES**

MACHINED BOARD STACKING STRIPS

Mates with:SS, SD, HSS, SL, SDL,
ESS, ESD**FEATURES**

- Low profile design achieves (3.89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:
Black Liquid Crystal Polymer (BBL, BHS)
Black Glass Filled Polyester (BBS, BBD, BDL)

Temperature Range:
-55 °C to +125 °C

Terminal Material:
Phosphor Bronze or Brass

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Lead-Free Solderable:
Yes (BBL, BDL, BHS-S)

No, Lead Wave only
(BBS, BBD, BHS-N)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note:
Some lengths, styles and options are non-standard, non-returnable.

