


PortaCrimp Dies




One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent & accurate with a parallel action stroke, good to 50,000 cycles.




431 50 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-1 .110" (2.8mm) tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 50	0.5-1.0/0.25-0.5/0.1-0.25mm ²	26-18	1.2	1




431 51 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-2 .187" (4.8mm) tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 51	1.5-2.5 & 0.5-1.5mm ²	22-14	1.2	1



431 43 PortaCrimp Weather Pack Open Barrel Terminals

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 43	4.0-1.0mm ²	12-20	1.2	1



431 41 PortaCrimp Fiber Optic Die set for SMA, SMB, SFR, ST, SC fiber optic connectors (.178"/.213"/.151"/.128" hex)


Item				
No.	Crimps		lbs.	Pkg.
431 41	4.52/5.41/3.84/3.25mm	(.178"/.213"/.151"/.128")	1.2	1



431 36 PortaCrimp Coaxial Network & Communications


Die set for RG58, RG59, RG62AU BNC/TNC Coaxial Connectors (.213"/.255"/.068" hex).

Item	Crimps		
No.	1.69/5.41/6.48mm	lbs.	Pkg.
431 36	(.213"/.255"/.068" hex)	1.2	1



431 38 PortaCrimp Coaxial Network & Communications, CATV, HDTV, Video Die set for RG6, Belden 1694A, Twinax BNC, CATV F Coaxial Connectors (.360"/.324" Hex).


Item			
No.	Crimps	lbs.	Pkg.
431 38	9.14 & 8.23mm (.360"/.324")	1.2	1



431 40 PortaCrimp Coaxial Network & Communications

Die set for RG174, RG179 BNC/TNC Coaxial Connectors (.178"/.128"/.068" Hex, .028" (0.7mm) Sq).

Item	Crimps		
No.	4.52/3.25/1.69mm hex 0.7mm sq.	lbs.	Pkg.
431 40	(.178"/.128"/.068" hex, .028" sq.)	1.2	1



431 44 PortaCrimp Datacom/Telecom Modular Plug Die set for 8-position 8-contact (RJ45).

Item			
No.	RJ45	lbs.	Pkg.
431 44		1.2	1