

Infinity™ Case



With flair, style and professional presence, the Infinity is the newest generation of Ameripack blow molded cases, designed to give you the highest protection level possible.



The Infinity features a natural dust seal and double wall protection in the lid and base that naturally create an interior impact barrier helping the case become crush resistant and withstand a 30 pound impact test. The dual latch system provides easy latching with confidence of security even in the harshest conditions.



Infinity Pin Hinge



Empty

Convoluted & Flat

Convoluted & Diced

Offered with or without foam, the Infinity is available in a variety of sizes and depths.




The Infinity lends itself to customization including engraving, printing, labeling, die-cut foam, custom colors and the new in-mold labeling/decorating process (see overview pages iv & v). Made of high-density polyethylene (HDPE) the case is impervious to most chemicals, gasoline and is an excellent case in most applications.



Infinity Locking Hole

Drawing Key

a = Exterior Length
b = Exterior Width
c = Overall Exterior Depth
d = Interior Length
e = Interior Width
f = Overall Interior Depth
g = Interior Lid Depth
h = Interior Base Depth



Infinity™ Cases

This blow molded case with double wall construction gives you the highest protection level possible.

- Offered with or without foam
- Select styles available in integral or pin hinge.



Stock Number	Style	Interior Dimensions L x W x overall D (d x e x f) inches (cm)	Interior Depth Lid = g Base = h inches (cm)	Exterior Dimensions L x W x overall D (a x b x c) inches (cm)	Standard Handle / Latch	Description inches (cm)
20190 50190 	FH 4	8-1/4 x 5-7/16 x 3-5/16 (20.96 x 13.81 x 8.41)	g = 1-5/16 (3.33) h = 1-15/16 (4.92)	10-1/8 x 8-1/8 x 4 (25.72 x 20.64 x 10.16)	H052 / L089	foam option available
20250 50250 	FQ 2-1/2	9-1/2 x 6-5/8 x 1-3/4 (24.13 x 16.83 x 4.45)	g = 3/8 (0.95) h = 1-3/8 (3.49)	12 x 9 x 2-1/2 (30.48 x 22.86 x 6.35)	H052 / L089	foam option available
20290 50290 	FQ 4-1/2	9-1/2 x 6-5/8 x 4-13/16 (24.13 x 16.83 x 12.22)	g = 2-7/16 (6.19) h = 2-3/8 (6.03)	12 x 9 x 4-1/2 (30.48 x 22.86 x 11.43)	H052 / L089	foam option available
20330 50330 	FV 4	11-3/4 x 8-1/8 x 3-3/16 (29.85 x 20.64 x 8.10)	g = 1-3/8 (3.49) h = 1-13/16 (4.60)	14 x 10-1/2 x 4 (35.56 x 26.67 x 10.16)	H052 / L089	foam option available
20350 50350 	FV 5	11-1/2 x 8-1/2 x 4-1/4 (29.21 x 21.59 x 10.80)	g = 1-7/8 (4.76) h = 2-3/8 (6.03)	14 x 10-1/2 x 5 (35.56 x 26.67 x 12.70)	H052 / L089	Integral Hinge foam option available
20351 50351 	FV 5	11-1/2 x 8-1/2 x 4-1/4 (29.21 x 21.59 x 10.80)	g = 1-7/8 (4.76) h = 2-3/8 (6.03)	14 x 10-1/2 x 5 (35.56 x 26.67 x 12.70)	H052 / L089	Pin Hinge foam option available
20410 50410 	FW 4-1/2	14-3/8 x 10 x 3-7/16 (36.51 x 25.40 x 8.73)	g = 1-1/4 (3.18) h = 2-3/16 (5.56)	17 x 14-1/2 x 4-1/2 (43.18 x 36.83 x 11.43)	H023 / L085	foam option available
20430 50430 	FW 6-1/2	14-1/8 x 9-7/8 x 5-9/16 (35.88 x 25.08 x 14.13)	g = 2-5/16 (5.87) h = 3-1/4 (8.26)	17 x 14-1/2 x 6-1/2 (43.18 x 36.83 x 16.51)	H023 / L085	foam option available
20470 50470 	FX 5-1/2	17-3/4 x 12-5/8 x 4-1/16 (45.09 x 32.07 x 10.32)	g = 1-13/16 (4.60) h = 2-1/4 (5.72)	20 x 15 x 5-1/2 (50.80 x 38.10 x 13.97)	H023 / L095	foam option available
20474 50474 	FX 5-1/2	17-3/4 x 12-5/8 x 4-1/16 (45.09 x 32.07 x 10.32)	g = 1-13/16 (4.60) h = 2-1/4 (5.72)	20 x 15 x 5-1/2 (50.80 x 38.10 x 13.97)	H023 / L078	With pallet strap foam option available
20500 50500 	FX 8-1/2	16-3/4 x 11-7/8 x 7-1/2 (42.55 x 30.16 x 19.05)	g = 3-1/4 (8.26) h = 4-1/4 (10.80)	20 x 15 x 8-1/2 (50.80 x 38.10 x 21.59)	H023 / L095	foam option available