



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D



TERMINATED VIEW

C




HOUSING

CONTACT

COVER

A SPACES AT .050 STAGGERED SPACING
=B REF

B



.629 REF
BEFORE
TERMINATION

1 UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.


2 PHOSPHOR BRONZE PER QQ-B-750.

3 PLATED WITH .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000015 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.

4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.

LOCALIZED GOLD
PLATING ON THIS SURFACE

.014 MIN LOCALIZED
GOLD PLATE AREA



DETAIL Z
SCALE 10:1
TYPICAL

OBSOLETE

3.100	3.380	3.150	63	64	1-1658620-2
2.900	3.180	2.950	59	60	1-1658620-1
2.400	2.680	2.450	49	50	1-1658620-0
1.900	2.180	1.950	39	40	1658620-9
1.600	1.880	1.650	33	34	1658620-8
1.400	1.680	1.450	29	30	1658620-7
1.200	1.480	1.250	25	26	1658620-6
1.100	1.380	1.150	23	24	1658620-5
.900	1.180	.950	19	20	1658620-4
.700	.980	.750	15	16	1658620-3
.600	.880	.650	13	14	1658620-2
.400	.680	.450	9	10	1658620-1
D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SAMICK 22AUG03		 TE Connectivity	
		CHK C. ROHDE 22AUG03			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD M. WALMSLEY 22AUG03		RECEPTACLE ASSY, MILITARY POLARIZATION, LEAD FREE, AMP-LATCH™ NOVO	
		PRODUCT SPEC 108-40000			
		APPLICATION SPEC 114-40005			
		WEIGHT —			
		CUSTOMER DRAWING			
MATERIAL		FINISH		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=1658620	
				RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 of 1	
				REV D1	