

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19141-0023
Status: Active
Overview: Solderless Terminals
Description: Krimptite™ Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-015 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series 19141
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Solderless Terminals
Product Name Krimptite™
Type Spade
UPC 800753103207

Physical

Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Net Weight 0.374/g
Packaging Type Adhesive Tape on Reel
Stud Size 8 (M4)
Wire Size AWG 18, 20, 22
Wire Size mm² 0.25 - 1.50

Electrical

Voltage - Maximum 600V

Material Info

Old Part Number AA-135-08T

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-015
Sales Drawing AACD10303




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19141Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Mini-Mac™ Applicator	0638853800
ATP Tooling Kit for ATP-100 and ATP-300 Series Air Crimping Press for Mylar Tape Mounted Terminals	0190270034

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19141-0023](#)