




These Open Former Differential Mode Suppression Chokes, are specifically designed to attenuate mains borne RF interference.

Constructed using a single wound ferrite ring mounted vertically onto a flame retardant plastic carrier.



CHARACTERISTICS	
Voltage Range :	250 VAC
Live Frequency :	50 / 60Hz
Temperature Range :	-25°C to 85°C
Inductance Tolerance :	± 20%
Temperature Rise @ Rated Current :	30°C

PCB Drilling Detail



PART No.	AMP	INDUCTANCE	D.C. RESISTANCE (mΩ)
DF1	1	1.17 mH	1470
DF2	2	0.5 mH	370
DF3	3	0.26 mH	140
DF4	4	0.21 mH	100
DF5	6	0.12 mH	40
DF6	8	0.085 mH	25