


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	S0		P	REV PER ECO 07-019087	8-16-07	CT	DE

PART NO.	A 		
839565-1	12.00	[304.8]	
839565-2	81.00	[2057.4]	OBSOLETE
839565-3	64.00	[1625.6]	OBSOLETE
839565-4	47.00	[1193.8]	OBSOLETE
839565-5	20.00	[508.0]	OBSOLETE
839565-6	48.00	[1219.2]	
839565-7	120.00	[3048.0]	
839565-8	16.00	[406.4]	OBSOLETE
839565-9	24.00	[609.6]	
1-839565-0	71.00	[1803.4]	OBSOLETE
1-839565-1	300.00	[7620.0]	OBSOLETE
1-839565-2	72.00	[1828.8]	OBSOLETE
1-839565-3	8.00	[203.2]	
1-839565-4	150.00	[3810.0]	OBSOLETE
1-839565-5	39.00	[990.6]	OBSOLETE
1-839565-6	354.00	[8991.6]	OBSOLETE
1-839565-7	708.00	[17983.2]	OBSOLETE
1-839565-8	22.00	[558.8]	OBSOLETE
1-839565-9	26.00	[660.4]	OBSOLETE
2-839565-0	37.38	[949.5]	OBSOLETE
2-839565-1	30.12	[765.0]	OBSOLETE
2-839565-2	40.00	[1016.0]	
2-839565-3	50.00	[1270.0]	OBSOLETE
2-839565-4	31.50	[800.1]	OBSOLETE
2-839565-5	36.00	[914.4]	
2-839565-6	600.00	[15240.0]	OBSOLETE
2-839565-7	44.00	[1117.6]	OBSOLETE
2-839565-8	13.00	[330.2]	
2-839565-9	18.00	[457.2]	
3-839565-0	30.00	[762.0]	
3-839565-1	11.00	[279.4]	
3-839565-2	9.00	[228.6]	
3-839565-3	10.00	[254.0]	
3-839565-4	240.00	[6096.0]	



-  TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
2. MARKED PER MIL-STD-130.
3. TO MATE WITH AMP LGH-2
RECEPTACLE WITH 1.43 [36.3] BARREL DEPTH.
4. OPERATING VOLTAGE: 30 KVDC AT 0 TO 70,000 FEET, -55° TO +125°C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	6-15-90	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK	7-11-90				
DIMENSIONS: INCHES [mm]		APVD	7-11-90	NAME LEAD ASS'Y, DBL. END, LGH-2			
		PRODUCT SPEC					
		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS	WEIGHT	A2	00779	C=839565	-
			CUSTOMER DRAWING	SCALE	1:1	SHEET	1 of 1
						REV	P