

MODEL TL-2100


International size reference: AA, ER14505

TECHNICAL DATA

(Typical values @+25°C for batteries stored for one year or less)



| | |
|--|-----------------|
| ■ Nominal capacity @ 2 mA, to 2V | 2.1 Ah |
| ■ Rated voltage | 3.6 V |
| ■ Maximum recommended continuous current | 120 mA |
| ■ Maximum pulse current capability | 200 mA |
| ■ Weight | 17.6g (0.62 oz) |
| ■ Volume | 8 cc |
| ■ Operating temperature range | -55°C to +85°C |
| ■ U.L. Component Recognition, MH 12193 | |

TADIRAN LITHIUM BATTERIES



AVAILABLE TERMINATIONS

| | |
|----------------------------|---------------|
| SUFFIX- /S STANDARD | 15-5103-21500 |
| SUFFIX- /T SOLDER TABS | 15-5103-31500 |
| SUFFIX- /P AXIAL PINS | 15-5103-41500 |
| SUFFIX- /PT2 RADIAL PINS | 15-5103-36500 |
| SUFFIX- /TP POLARIZED TABS | 15-5103-52500 |
| SUFFIX- /PT POLARIZED TABS | 15-5103-53500 |



LITHIUM XTRA

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance. Rev. B 04/03