





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER ECO-16-010367	14JUL2016	DS	SY

6	187.96 [7.400]	74	191.11 [7.524]	201.93 [7.950]	209.55 [8.250]	300	1-5532434-2
7	175.26 [6.900]	69	178.41 [7.024]	189.23 [7.450]	196.85 [7.750]	280	1-5532434-1
8	149.86 [5.900]	59	153.01 [6.024]	163.83 [6.450]	171.45 [6.750]	240	5532434-9
	137.16 [5.400]	54	140.31 [5.524]	151.13 [5.950]	158.75 [6.250]	220	5532434-8
	124.46 [4.900]	49	127.61 [5.024]	138.43 [5.450]	146.05 [5.750]	200	5532434-7
8	111.76 [4.400]	44	114.91 [4.524]	125.73 [4.950]	133.35 [5.250]	180	5532434-6
	99.06 [3.900]	39	102.21 [4.024]	113.03 [4.450]	120.65 [4.750]	160	5532434-5
	86.36 [3.400]	34	89.51 [3.524]	100.33 [3.950]	107.95 [4.250]	140	5532434-4
8	60.96 [2.400]	24	64.11 [2.524]	74.93 [2.950]	82.55 [3.250]	100	5532434-1
	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. POLIGNONE	10JUN05	 TE Connectivity				
DIMENSIONS: mm [INCHES]			CHK A. SHARPE	10JUN05					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD A. SHARPE	10JUN05	NAME				
			PRODUCT SPEC		ASSY, REC, RIGHT ANGLE, HDI LEAD FREE, 4 ROW, W/O GUIDES 4.57[.180] SOLDER POSTS				
			APPLICATION SPEC						
			SIZE					CAGE CODE	DRAWING NO
			WEIGHT					0.000000	
MATERIAL			CUSTOMER DRAWING		RESTRICTED TO				
 					A1 00779  5532434				
FINISH			SCALE		4:1				
			SHEET		1 of 1				
			REV		A				