



# Datasheet for part number 115394-1000

Our Catalog Part Number: DEW-9P-2
Our Global Manufacturing Part Number: 115394-1000
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*W

Product Datasheet	
General	Connector with IDC technology - stranded or solid wires could be terminated
Wire Gauge Range AWG	AWG 22-26
Mating Cycles	50
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	3 A (AWG 20) - 0.8 A (AWG 30)
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	9 contacts size 20
Gender	Pin
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Contact Termination	IDC
Mounting Methode	.120" (3,05mm) Through Hole