


Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-1828	T-3¼	BA9s	37.5V 50mA	C-2F

Test Volts	Current (mA)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max	
37.5	45	50	55	.487	.650	.813	3,000 Hrs

Dimensional Characteristics:

1. L.C.L = .63" (16mm)
2. Base = Nickel-plated Brass Construction
3. ANSI Standard. No. 1828
4. Part Mark: WL-1828



			Title: T-3¼ Miniature Bayonet Base Lamp 37.5V 50mA Vacuum	
Drawn	01/24/12	SL	Notes: Unless otherwise specified, all dimensions are in mm.	Rev: 1
Checked	01/24/12	EB		
Approved	01/24/12	EB		