




13			12		11		10		9		8		7		6		5		4		3		2		1									
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK							
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES W/ VAC CAPS				TUBES		TUBES					
			DIM. M±0.25 MM				6.10 (.240)								6.10 (.240)								6.10 (.240)								8.13 (.320)		8.13 (.320)	
			PLATING				150 TIN								15 GOLD				30 GOLD								15 GOLD				30 GOLD			
			DIM. H				2.54 (.100)								2.54 (.100)				2.54 (.100)								4.57 (.180)				4.57 (.180)			
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS							
	MM	IN	MM	IN																														
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A	015-91-0048	015-91-5049	04																		
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A	015-91-0068	015-91-5069	06																		
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088	015-91-0088	015-91-5089	08																		
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108	015-91-0108	015-91-5109	10																		
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128	015-91-0128	015-91-5129	12																		
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148	015-91-0148	015-91-5149	14																		
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168	015-91-0168	015-91-5169	16																		
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188	015-91-0188	015-91-5189	18																		
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208	015-91-0208	015-91-5209	20																		
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228	015-91-0228	015-91-5229	22																		
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248	015-91-0248	015-91-5249	24																		
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268	015-91-0268	015-91-5269	26																		
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288	015-91-0288	015-91-5289	28																		
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308	015-91-0308	015-91-5309	30																		
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328	015-91-0328	015-91-5329	32																		
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348	015-91-0348	015-91-5349	34																		
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368	015-91-0368	015-91-5369	36																		
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388	015-91-0388	015-91-5389	38																		
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408	015-91-0408	015-91-5409	40																		
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428	015-91-0428	015-91-5429	42																		
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448	015-91-0448	015-91-5449	44																		
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468	015-91-0468	015-91-5469	46																		
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488	015-91-0488	015-91-5489	48																		
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508	015-91-0508	015-91-5509	50																		
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528	015-91-0528	015-91-5529	52																		
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548	015-91-0548	015-91-5549	54																		
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568	015-91-0568	015-91-5569	56																		
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588	015-91-0588	015-91-5589	58																		
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608	015-91-0608	015-91-5609	60																		
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628	015-91-0628	015-91-5629	62																		
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648	015-91-0648	015-91-5649	64																		
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668	015-91-0668	015-91-5669	66																		
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688	015-91-0688	015-91-5689	68																		
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708	015-91-0708	015-91-5709	70																		
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728	015-91-0728	015-91-5729	72																		
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748	015-91-0748	015-91-5749	74																		
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768	015-91-0768	015-91-5769	76																		
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788	015-91-0788	015-91-5789	78																		
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808	015-91-0808	015-91-5809	80																		
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682	71308-1182	71308-1282	82																		
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684	71308-1184	71308-1284	84																		
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686	71308-1186	71308-1286	86																		
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688	71308-1188	71308-1288	88																		
90	114.30	4.500																																

13		12		11		10		9		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE										BULK / IN TUBES										J			
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS									BULK		BULK								
				10-100 CKT	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS									TUBES		TUBES								
		DIM. M±0.25 MM		6.10 (.240)		6.10 (.240)								8.13 (.320)		13.59 (.535)									
		PLATING		30 GOLD		15 GOLD								150 TIN		150 TIN									
		DIM. H		2.54 (.100)		2.54 (.100)								4.57 (.180)		4.57 (.180)									
I		CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER					EDP NUMBER	EDP NUMBER	CKTS										
			MM	IN	MM	IN																			
H		04	5.08	.200	2.54	.100	015-91-6148						713088010	71308-8210											
		06	7.62	.300	5.08	.200			015-91-6068																
		08	10.16	.400	7.62	.300			015-91-6088																
		10	12.70	.500	10.16	.400			015-91-6108																
		12	15.24	.600	12.70	.500																			
		14	17.78	.700	15.24	.600																			
		16	20.32	.800	17.78	.700																			
		18	22.86	.900	20.32	.800																			
		20	25.40	1.000	22.86	.900																			
		22	27.94	1.100	25.40	1.000																			
G		24	30.48	1.200	27.94	1.100																			
		26	33.02	1.300	30.48	1.200																			
		28	35.56	1.400	33.02	1.300																			
		30	38.10	1.500	35.56	1.400																			
		32	40.64	1.600	38.10	1.500																			
		34	43.18	1.700	40.64	1.600																			
		36	45.72	1.800	43.18	1.700																			
		38	48.26	1.900	45.72	1.800																			
		40	50.80	2.000	48.26	1.900																			
		42	53.34	2.100	50.80	2.000																			
F		44	55.88	2.200	53.34	2.100																			
		46	58.42	2.300	55.88	2.200																			
		48	60.96	2.400	58.42	2.300																			
		50	63.50	2.500	60.96	2.400																			
		52	66.04	2.600	63.50	2.500																			
		54	68.58	2.700	66.04	2.600																			
		56	71.12	2.800	68.58	2.700																			
		58	73.66	2.900	71.12	2.800																			
		60	76.20	3.000	73.66	2.900																			
		62	78.74	3.100	76.20	3.000																			
E		64	81.28	3.200	78.74	3.100																			
		66	83.82	3.300	81.28	3.200																			
		68	86.36	3.400	83.82	3.300																			
		70	88.90	3.500	86.36	3.400																			
		72	91.44	3.600	88.90	3.500																			
		74	93.98	3.700	91.44	3.600																			
		76	96.52	3.800	93.98	3.700																			
		78	99.06	3.900	96.52	3.800																			
		80	101.60	4.000	99.06	3.900																			
		82	104.14	4.100	101.60	4.000																			
D		84	106.68	4.200	104.14	4.100																			
		86	109.22	4.300	106.68	4.200																			
		88	111.76	4.400	109.22	4.300																			
		90	114.30	4.500	111.76	4.400																			
		92	116.84	4.600	114.30	4.500																			
		94	119.38	4.700	116.84	4.600																			
		96	121.92	4.800	119.38	4.700																			
		98	124.46	4.900	121.92	4.800																			
		100	127.00	5.000	124.46	4.900																			
		B		NO PEG VERSION (ALSO SEE SHEET 2)										SEE SHEET 1 EC NO: UCP2015-0081 DRAWN BY: CHKD-NGUYEN CHKD-NGUYEN APPR: FSMITH 2014/05/22 2014/11/26 2015/01/08		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
4 PLACES ± --- mm ± --- INCH																	DRAWN BY DATE KMS 1999/10/15		TITLE	SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100					
A		3 PLACES ± --- mm ±.005 INCH		CHECKED BY DATE KMS 1999/10/15		1 PLACES ±0.13 ±.010		APPROVED BY DATE KMS 1999/10/15		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6													
		2 PLACES ±0.25 ± ---		MATERIAL NO. SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1	

13			12		11		10		9		8		7		6		5		4		3		2		1							
PACKAGING SEE NOTE 4 SHT 1							4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK							
							10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES							
							DIM. M±0.25 MM						6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)		8.13 (.320)			
							PLATING						150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD		30 GOLD			
							DIM. H						2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)		4.57 (.180)			
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS						
	MM	IN	MM	IN	MM	IN																										
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040											04						
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060											06						
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080											08						
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100											10						
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120											12						
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140											14						
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160											16						
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180											18						
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200											20						
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220											22						
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240											24						
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260											26						
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280											28						
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300											30						
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320											32						
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340											34						
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360											36						
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380											38						
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400											40						
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420											42						
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440											44						
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460											46						
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480											48						
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500											50						
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520											52						
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540											54						
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560											56						
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580											58						
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600											60						
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620											62						
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640											64						
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660											66						
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680											68						
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700											70						
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720											72						
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740											74						
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760											76						
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780											78						
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800											80						
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282											82						
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284											84						
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286											86						
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288											88						
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290											90						
92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092	</																								

	13	12	11	10	9	8	7	6	5	4	3	2	1							
J			PACKAGING SEE NOTE 4 SHT 1	4-8 CKT	BULK	TAPE-N-REEL W/ VAC CAPS	BULK	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS					J						
10-100 CKT				TUBES	TAPE-N-REEL W/ VAC CAPS	TUBES	TAPE-N-REEL W/ VAC CAPS	TAPE-N-REEL W/ VAC CAPS												
DIM. M±0.25 MM			6.10 (.240)		6.10 (.240)		8.13 (.320)													
PLATING			30 GOLD		150 TIN		150 TIN													
DIM. H			2.54 (.100)		2.54 (.100)		4.57 (.180)													
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS					
		MM	IN	MM	IN	MM	IN													
	04	5.08	.200	2.54	.100	----	----	015-91-1048	015-91-6047						04					
	06	7.62	.300	5.08	.200	2.54	.100	015-91-1068	015-91-6067	71308-6106	71308-6206				06					
	08	10.16	.400	7.62	.300	5.08	.200	015-91-1088	015-91-6087	71308-6108	71308-6208				08					
	10	12.70	.500	10.16	.400	7.62	.300	015-91-1108	015-91-6107	71308-6110	71308-6210				10					
	12	15.24	.600	12.70	.500	10.16	.400	015-91-1128							12					
	14	17.78	.700	15.24	.600	12.70	.500	015-91-1148	015-91-6147						14					
	16	20.32	.800	17.78	.700	15.24	.600	015-91-1168	015-91-6167						16					
	18	22.86	.900	20.32	.800	17.78	.700	015-91-1188							18					
	20	25.40	1.000	22.86	.900	20.32	.800	015-91-1208	015-91-6207						20					
	22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1228							22					
	24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1248							24					
	26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1268		71308-6126		71308-8426			26					
	28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1288							28					
	30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1308							30					
	32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1328							32					
	34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1348							34					
	36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1368							36					
	38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1388							38					
	40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1408							40					
	42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1428							42					
	44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1448							44					
	46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1468							46					
	48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1488							48					
	50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1508	015-91-6507						50					
	52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1528							52					
	54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1548							54					
	56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1568							56					
	58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1588							58					
	60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1608							60					
	62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1628							62					
	64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1648							64					
	66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1668							66					
	68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1688							68					
	70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1708							70					
	72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1728							72					
	74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1748							74					
	76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1768							76					
	78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1788							78					
	80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1808							80					
	82	104.14	4.100	101.60	4.000	99.06	3.900	71308-6082							82					
	84	106.68	4.200	104.14	4.100	101.60	4.000	71308-6084							84					
	86	109.22	4.300	106.68	4.200	104.14	4.100	71308-6086							86					
	88	111.76	4.400	109.22	4.300	106.68	4.200	71308-6088							88					
	90	114.30	4.500	111.76	4.400	109.22	4.300	71308-6090							90					
	92	116.84	4.600	114.30	4.500	111.76	4.400	71308-6092							92					
	94	119.38	4.700	116.84	4.600	114.30	4.500	71308-6094							94					
	96	121.92	4.800	119.38	4.700	116.84	4.600	71308-6096							96					
	98	124.46	4.900	121.92	4.800	119.38	4.700	71308-6098							98					
	100	127.00	5.000	124.46	4.900	121.92	4.800	71308-6100							100					
B	SHORT PEG VERSION (.055")														B					
A															A					
REMOVE 15-91-6407 EC NO: UCP2015-0081 DRAWN/KIPPER 2014/05/22 CHKD/NGUYEN 2014/11/26 APPR/FSMITH 2015/01/08		REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100 molex SD-71308-001		SHEET NO. 5 OF 6					
				▽=0 ▽=0 ▽=0	4 PLACES ± --- ± --- 3 PLACES ± --- ±.005 2 PLACES ± 0.13 ±.010 1 PLACE ± 0.25 ± --- 0 PLACE ± --- ± ---		DRAWN BY DATE KMS 1999/10/15 CHECKED BY DATE KMS 1999/10/15 APPROVED BY DATE KMS 1999/10/15													
					ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-71308-001											
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SIZE																		
tb_frame_C_P_AM,T Rev. G 2012/01/11		12	11	10	9	8	7	6	5	4	3	2	1							

		13		12		11		10		9		8		7		6		5		4		3		2		1											
J		PEG OPTION																								J											
		NO PEG VERSION														NO PEG VERSION				LONG PEG VERSION (.130")				SHORT PEG VERSION (.055")													
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A				4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS				BULK		BULK		TAPE-N-REEL W/ VAC CAPS					
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		TAPE-N-REEL W/VAC CAPS				TUBES		BULK		TAPE-N-REEL W/ VAC CAPS					
				DIM. M±0.25 MM				6.10 (.240)												8.13(.320)				13.59(.535)				6.10(.240)				8.13(.320)				6.10 (.240)	
I		PLATING				59 TIN												59 TIN				59 TIN				59 TIN				59 TIN							
		DIM. H				2.54(.100)												4.57(.180)				4.57(.180)				2.54(.100)				2.54(.100)							
CKTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER				EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS							
		MM	IN	MM	IN	MM	IN																														
04		5.08	.200	2.54	.100	---	---	71308-5404	71308-5504	N/A										71308-6404	71308-6504	71308-6604				71308-6706	71308-6806		04								
06		7.62	.300	5.08	.200	2.54	.100	71308-5406	71308-5506	N/A										71308-6406	71308-6506	71308-6606	71308-6706	71308-6806					06								
08		10.16	.400	7.62	.300	5.08	.200	71308-5408	71308-5508	71308-5608										71308-6408	71308-6508	71308-6608	71308-6708	71308-6808					08								
10		12.70	.500	10.16	.400	7.62	.300	71308-5410	71308-5510	71308-5610				71308-5810	71308-5910					71308-6410	71308-6510	71308-6610	71308-6710	71308-6810					10								
12		15.24	.600	12.70	.500	10.16	.400	71308-5412	71308-5512	71308-5612										71308-6412		71308-6612							12								
14		17.78	.700	15.24	.600	12.70	.500	71308-5414	71308-5514	71308-5614										71308-6414	71308-6514	71308-6614							14								
16		20.32	.800	17.78	.700	15.24	.600	71308-5416	71308-5516	71308-5616				71308-5816						71308-6416	71308-6516	71308-6616							16								
18		22.86	.900	20.32	.800	17.78	.700	71308-5418		71308-5618										71308-6418		71308-6618							18								
20		25.40	1.000	22.86	.900	20.32	.800	71308-5420	71308-5520	71308-5620										71308-6420		71308-6620							20								
22		27.94	1.100	25.40	1.000	22.86	.900	71308-5422		71308-5622										71308-6422		71308-6622							22								
24		30.48	1.200	27.94	1.100	25.40	1.000	71308-5424		71308-5624			71308-5724	71308-5824						71308-6424		71308-6624							24								
26		33.02	1.300	30.48	1.200	27.94	1.100	71308-5426		71308-5626										71308-6426		71308-6626	71308-6726						26								
28		35.56	1.400	33.02	1.300	30.48	1.200	71308-5428		71308-5628										71308-6428		71308-6628							28								
30		38.10	1.500	35.56	1.400	33.02	1.300	71308-5430		71308-5630										71308-6430		71308-6630							30								
32		40.64	1.600	38.10	1.500	35.56	1.400	71308-5432		71308-5632										71308-6432		71308-6632							32								
34		43.18	1.700	40.64	1.600	38.10	1.500	71308-5434		71308-5634										71308-6434		71308-6634							34								
36		45.72	1.800	43.18	1.700	40.64	1.600	71308-5436		71308-5636										71308-6436		71308-6636							36								
38		48.26	1.900	45.72	1.800	43.18	1.700	71308-5438		71308-5638										71308-6438		71308-6638							38								
40		50.80	2.000	48.26	1.900	45.72	1.800	71308-5440	71308-5540	71308-5640										71308-6440		71308-6640							40								
42		53.34	2.100	50.80	2.000	48.26	1.900	71308-5442		71308-5642										71308-6442		71308-6642							42								
44		55.88	2.200	53.34	2.100	50.80	2.000	71308-5444		71308-5644										71308-6444		71308-6644							44								
46		58.42	2.300	55.88	2.200	53.34	2.100	71308-5446		71308-5646										71308-6446		71308-6646							46								
48		60.96	2.400	58.42	2.300	55.88	2.200	71308-5448		71308-5648										71308-6448		71308-6648							48								
50		63.50	2.500	60.96	2.400	58.42	2.300	71308-5450	71308-5550	71308-5650										71308-6450	71308-6550	71308-6650							50								
52		66.04	2.600	63.50	2.500	60.96	2.400	71308-5452		71308-5652										71308-6452		71308-6652							52								
54		68.58	2.700	66.04	2.600	63.50	2.500	71308-5454		71308-5654										71308-6454		71308-6654							54								
56		71.12	2.800	68.58	2.700	66.04	2.600	71308-5456		71308-5656										71308-6456		71308-6656							56								
58		73.66	2.900	71.12	2.800	68.58	2.700	71308-5458		71308-5658										71308-6458		71308-6658							58								
60		76.20	3.000	73.66	2.900	71.12	2.800	71308-5460		71308-5660										71308-6460		71308-6660							60								
62		78.74	3.100	76.20	3.000	73.66	2.900	71308-5462		71308-5662										71308-6462		71308-6662							62								
64		81.28	3.200	78.74	3.100	76.20	3.000	71308-5464		71308-5664										71308-6464		71308-6664							64								
66		83.82	3.300	81.28	3.200	78.74	3.100	71308-5466		71308-5666										71308-6466		71308-6666							66								
68		86.36	3.400	83.82	3.300	81.28	3.200	71308-5468		71308-5668										71308-6468		71308-6668							68								
70		88.90	3.500	86.36	3.400	83.82	3.300	71308-5470		71308-5670										71308-6470		71308-6670							70								
72		91.44	3.600	88.90	3.500	86.36	3.400	71308-5472		71308-5672										71308-6472		71308-6672							72								
74		93.98	3.700	91.44	3.600	88.90	3.500	71308-5474		71308-5674										71308-6474		71308-6674							74								
76		96.52	3.800	93.98	3.700	91.44	3.600	71308-5476		71308-5676										71308-6476		71308-6676							76								
78		99.06	3.900	96.52	3.800	93.98	3.700	71308-5478		71308-5678										71308-6478		71308-6678							78								
80		101.60	4.000	99.06	3.900	96.52	3.800	71308-5480		71308-5680										71308-6480		71308-6680							80								
82		104.14	4.100	101.60	4.000	99.06	3.900	71308-5482		71308-5682										71308-6482		71308-6682							82								
84		106.68	4.200	104.14	4.100	101.60	4.000	71308-5484		71308-5684										71308-6484		71308-6684							84								
86		109.22	4.300	106.68	4.200	104.14	4.100	71308-5486		71308-5686										71308-6486		71308-6686							86								
88		111.76	4.400	109.22	4.300	106.68	4.200	71308-5488		71308-5688										71308-6488		71308-6688							88								
90		114.30	4.500	111.76	4.400	109.22	4.300	71308-5490		71308-5690										71308-6490		71308-6690							90								
92		116.84	4.600	114.30	4.500	111.76	4.400	71308-5492		71308-5692																											