

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0795762104](#)
Status: **Active**
Overview: [iPass™](#)
Description: Internal iPass™ Mini SAS Double-Ended Plug with Sidebands, 36 Circuits, 28 AWG, 1.0m (3.28') Length, Controller-to-Backplane, Pinout 1

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	79576
Connector to Connector	iPass-to-iPass
Overview	iPass™
Product Name	iPass™
Product Name	Mini Multi-Lane
Product Name	PCI Express*
Product Name	SAS

Physical

Cable Length	1.0m (3.28')
Circuits (Loaded)	36
Color - Resin	Black
Color - Resin	Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Resin	Low Density Polyethylene
Material - Resin	Polyester
Packaging Type	Bag
Pitch - Mating Interface (in)	0.031 In
Pitch - Mating Interface (mm)	0.80 mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Twin-ax

Electrical

Current - Maximum	1A
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-79576-200
---------------	--------------



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Halogen-Free
Status**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[79576](#) Series

Mates With

[75783](#) iPass™ Right Angle Connector.
[75784](#) iPass™ Vertical Connector