



Specifications:


Models:	Code
DRS 3010	BCD
DRS 3110	BCD Inverse
DRS 3016	Hexadecimal
DRS 3116	Hexadecimal Inverse




DRS 4010	BCD
DRS 4110	BCD Inverse
DRS 4016	Hexadecimal
DRS 4116	Hexadecimal Inverse



DRR 3010	BCD
DRR 3110	BCD Inverse
DRR 3016	Hexadecimal
DRR 3116	Hexadecimal Inverse




DRR 4010	BCD
DRR 4110	BCD Inverse
DRR 4016	Hexadecimal
DRR 4116	Hexadecimal Inverse




Caps*

yellow	KR 108
red	KR 109
white	KR 110



grey KR 207




Subminiature Rotary Coded Switches for SMT



Specifications:

Contact rating:	50 V DC, 100 mA, non switching 15 V DC, 30 mA , switching
Contact resistance:	< 100 mΩ
Insulation resistance:	> 1000 MΩ at 250 V DC
Dielectric strength:	250 V, 50 Hz for the duration of 1 minute
Operating temperature:	- 20° to + 80° C
Mechanical life:	minimum 20 000 operations
Contacts:	phosphor bronze, gold-plated
Terminals:	phosphor bronze, tin-plated
Case material:	PPS black, rotor: standard types yellow; inverse types red
Construction:	case totally sealed with protective tape
Mounting:	on pc-board – SMD

Models:	Code
SMR 5010	BCD
SMR 5110	BCD Inverse



SMR 5016	Hexadecimal
SMR 5116	Hexadecimal Inverse



Soldering conditions:	reflow-line – max.: 40 sec, 200° C peak temperature: 230° C
-----------------------	--

Packaging:	sticks or tapes for order on tape: additional to type number: T example of order: SMR 5010 T
------------	--

Stick	Tape	Reel
50 pieces; L 530 mm	500 pieces	Ø 330 mm

