


Dimensions: in.
(except where noted)



■ SPECIFICATIONS:

- Primary voltage: 120VAC 60Hz
- Primary exciting current, open circuit: 50mA max. (no load),
100mA max. (loaded)
- Primary DC resistance \pm 15%: 127 Ω
- Secondary loaded voltage: 24VAC 500mA
- Secondary DC resistance \pm 10%: 4.6 Ω
- Insulation resistance: 100M Ω @ 500VDC
- Dielectric strength: 500VAC for 1 minute
- Polarity: center positive
- Output cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[412-224054](#)