

Datasheet

Art.No. 91.040.5953.0

Intermediate coupling GST15I4Z 1P1 V WS

Intermediate coupling, GST15i4, 4 pole, 1 input, 1 output, 250V/16A, for direct routing, color of coding: white



Art.No.	91.040.5953.0
EAN	4015573944923
Order unit	100 pieces

Approvals

Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	

Model

Number of poles	4
Number of inputs	1
Number of outputs	1
Type of fastening	No
Degree of protection (IP)	IP40
Type of distributor	Intermediate coupling

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	32.4 mm
Width	32 mm
Height	12.5 mm