

You are here: Products » Connectors f.con » PCB connectors » Male headers » SL 1 ... / SL 11 ... » SL 1 128

- ▶ Heatsinks f.cool
- ▶ Cases f.case
- ▼ **Connectors f.con**
 - ▶ Sockets
 - ▼ PCB connectors
 - Male headers
 - Female headers
 - Direct female connectors
 - Jumpers
 - ▶ IDC-connectors
 - ▶ D-Sub connectors
 - Brackets for PC
 - ▶ Optoelectronics

Male headers


SL 1 ... / SL 11 ...

SL 1 128 25 G

one row, □ 0.635 mm

Data sheet

add to request



Features Technical Drawing Variants Service Accessories / related products

grid	2.54 mm
no. of contacts	25
contact material	CuSn alloy
surface of contact	gold-plated
surface contact / contact sleeve	Ni+≥0.2µm Au
	Ni+4...6µm Sn
version	standard
volume resistance	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of inflammability	UL 94 V-0
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	-
reflow solderable	yes