



Tolerance


7/8


 $\phi 10.4 \pm 0.4$ 

3



49.5 ± 0.5



Nominal voltage 1.2 V  
 Nominal capacity 650mAh  
 Approx. weight 14g  
 Charged state

|      |                  |                 |     |         |        |
|------|------------------|-----------------|-----|---------|--------|
| 3    | Jacket           | P. V. C tube    | 1   |         |        |
| 2    | Insulation ring  | Paper           | 1   |         |        |
| 1    | Battery          | HHR65AAA        | 1   |         |        |
| Sym. | Item or Code No. | Material & Size | qt. | Process | Remark |

|       |            |            |              |           |      |           |                                     |  |
|-------|------------|------------|--------------|-----------|------|-----------|-------------------------------------|--|
|       |            |            |              |           | Name |           | Sealed Nickel Metal Hydride Battery |  |
|       |            |            |              |           |      |           | HHR-65TAB17                         |  |
| Scale | Designed   | Drawn      | Checked      | Approved  | No.  | C21072096 |                                     |  |
| 1/1   | SUGIMOTO   | SUGIMOTO   | O. Katsumata | R.Y. SATO |      |           |                                     |  |
|       | 14 MAY. 97 | 14 MAY. 97 |              |           |      |           |                                     |  |