

BMP®51 and BMP®53 Materials

www.BradyID.com/bmp51

BMP®51 and BMP®53 General Identification Material:

B-584 Reflective Material

Highly reflective labels shine back brightly when struck by light.



Figure 33



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
Fig.33	MC-500-584	B-584	Reflective	BK on WT	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-750-584	B-584	Reflective	BK on WT	0.750 (19.05)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-1000-584	B-584	Reflective	BK on WT	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-1500-584	B-584	Reflective	BK on WT	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-500-584-YL	B-584	Reflective	BK on YL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-750-584-YL	B-584	Reflective	BK on YL	0.750 (19.05)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-1000-584-YL	B-584	Reflective	BK on YL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
Fig.33	MC-1500-584-YL	B-584	Reflective	BK on YL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)

BMP®51 and BMP®53 General Identification Material:

B-595 Indoor / Outdoor Vinyl Material

Pliable vinyl conforms well to smooth or rough surfaces such as pipes, panels, shelving, bins, and equipment. Excellent resistance to oils, detergents, dirt, grime, and many solvents. Label last up to 8-10 years outdoors.




Figure 33



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
Fig. 33	MC-500-595-WT-BK	B-595	Vinyl	BK on WT	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-WT-BK	B-595	Vinyl	BK on WT	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-WT-BK	B-595	Vinyl	BK on WT	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-WT-BK	B-595	Vinyl	BK on WT	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-YL-BK	B-595	Vinyl	BK on YL	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-YL-BK	B-595	Vinyl	BK on YL	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-YL-BK	B-595	Vinyl	BK on YL	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-YL-BK	B-595	Vinyl	BK on YL	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-OR-BK	B-595	Vinyl	BK on OR	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-OR-BK	B-595	Vinyl	BK on OR	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-OR-BK	B-595	Vinyl	BK on OR	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-OR-BK	B-595	Vinyl	BK on OR	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-BL-WT	B-595	Vinyl	WT on BL	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-BL-WT	B-595	Vinyl	WT on BL	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-BL-WT	B-595	Vinyl	WT on BL	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-BL-WT	B-595	Vinyl	WT on BL	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-RD-WT	B-595	Vinyl	WT on RD	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-RD-WT	B-595	Vinyl	WT on RD	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-RD-WT	B-595	Vinyl	WT on RD	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-RD-WT	B-595	Vinyl	WT on RD	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-GN-WT	B-595	Vinyl	WT on GN	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-GN-WT	B-595	Vinyl	WT on GN	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-GN-WT	B-595	Vinyl	WT on GN	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-GN-WT	B-595	Vinyl	WT on GN	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-WT-RD	B-595	Vinyl	RD on WT	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-WT-RD	B-595	Vinyl	RD on WT	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-WT-RD	B-595	Vinyl	RD on WT	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-WT-RD	B-595	Vinyl	RD on WT	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-BK-WT	B-595	Vinyl	WT on BK	0.500 (12.70)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-750-595-BK-WT	B-595	Vinyl	WT on BK	0.750 (19.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1000-595-BK-WT	B-595	Vinyl	WT on BK	1.000 (25.40)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-1500-595-BK-WT	B-595	Vinyl	WT on BK	1.500 (38.10)	25 ft. (7.62 m)	1 roll (cont.)
Fig. 33	MC-500-595-CL-BK	B-595	Vinyl	BK on CL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-750-595-CL-BK	B-595	Vinyl	BK on CL	0.750 (19.10)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-1000-595-CL-BK	B-595	Vinyl	BK on CL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-1500-595-CL-BK	B-595	Vinyl	BK on CL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-500-595-CL-WT	B-595	Vinyl	WT on CL	0.500 (12.70)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-750-595-CL-WT	B-595	Vinyl	WT on CL	0.750 (19.10)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-1000-595-CL-WT	B-595	Vinyl	WT on CL	1.000 (25.40)	20 ft. (6.09 m)	1 roll (cont.)
Fig. 33	MC-1500-595-CL-WT	B-595	Vinyl	WT on CL	1.500 (38.10)	20 ft. (6.09 m)	1 roll (cont.)

Full Material Properties on page 187.